

Portable Charger - 2x USB-A, 12,000mAh Power Bank, Lithium-Ion, Auto Sensing, Black

MODEL NUMBER: UPB-12K0-S2X2U



Compact 2-port 12,000mAh power bank charges multiple smartphones, tablets, e-readers, MP3 players and other handheld mobile devices anywhere, anytime, without plugging into an AC power outlet.

Features

Travel-Sized for Convenient Charging of Devices Anywhere

- Compact form fits comfortably in your purse or backpack
- Ideal for charging up to 2 smartphones, tablets, e-readers, MP3 players and other handheld mobile devices simultaneously
- Works with Android, Apple and Windows devices

Built-In 12,000mAh Lithium-Ion Battery Charges Without an AC Power Outlet

- Charges at maximum power draw for hours to ensure your devices are ready when you need them
- Dual USB ports provide up to 5V 2.4A of power
- Auto-sensing ports adjust amperage to match amperage of connected device
- Protects against short circuits, overvoltage, overcurrent, overcharges and overdischarges

Easy to Recharge for the Next Time You Leave Home or Office

- USB Micro-B port connects to USB charger or computer's USB-A port to charge internal battery
- Built-in LEDs indicate at a glance how much battery capacity is left
- 3 ft. USB Micro-B charging cable included

Highlights

- Dual USB-A ports provide up to 5V 2.4A of power
- Auto-sensing port adjusts amperage to match connected device
- LEDs indicate remaining battery capacity at a glance
- 3-ft. (0.91 m) USB Micro-B charging cable included
- Compact form fits comfortably in your purse or backpack

Package Includes

- UPB-12K0-S2X2U 12,000mAh Dual-Port Mobile Power Bank USB Battery Charger
- USB Micro-B cable, 3 ft.
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332203939
Product Type	Portable Charger
Charging Form Factor	Portable
Device Compatibility	Phone; Tablet; Amazon Kindle



Powering Business Worldwide



Country/Region	Global
INPUT	
Nominal Input Voltage(s) Supported	5V DC
Input Plug Type	USB MICRO-B (FEMALE)
Input Plug Type Details	USB-A to USB Micro B cable provided
OUTPUT	
Output Capacity (Watts)	12
Continuous Output Capacity (Watts)	12
Overload Protection	Yes
BATTERY	
Battery Charging (5V/1.5A Port)	No
Capacity (Ah)	12
POWER	
USB Power Delivery (PD) Charging Support	No
CONNECTIONS	
Side A - Connector 1	MICRO-USB B (FEMALE)
Side B - Connector 1	(2) USB A (FEMALE)
Connector Plating	Nickel
Contact Plating	Nickel
CHARGING	
Number of Charging Ports	2
Total Charging Amps	2.4A
Total Charging Watts	12
Charging Method	USB
Charging Method Detail	12,000 mAh
Charging Port Type	(2) USB A (FEMALE)
Charging Ports	(2) 2.4A Quick Charge
Charging Ports Details	USB-A: 5V/2.4A
Charging Ports / Amps	(2) 2.4A
Magnetic Charging	No
Wireless Charging	No
Smart Charging Details	(x2) 5V 2.4A charging ports auto sense power draw needed from connected device



Powering Business Worldwide



Compatible Devices	Portable Speaker; Smartphone; Tablet
Charging Amps per Port	2.4
PHYSICAL	
Color	Black
Material of Construction	ABS
Total Number of Ports	3
Unit Dimensions (hwd / in.)	5.500 x 2.500 x 1.000
Unit Dimensions (hwd / cm)	14 x 6.4 x 2.5
Unit Weight (lbs.)	0.60
Unit Weight (kg)	0.27
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	5° to 113°F (-15° to 45°C)
Relative Humidity	0% to 90% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
GaN Technology	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
Over Current Protection	Yes
Quick Charge Compliant	No
USB Hub Ports	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; CE (Europe); FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.