

## Portable 5000mAh 2-Port Mobile Power Bank and USB Battery Wall Charger Combo - Direct Plug, Black

MODEL NUMBER: UPBW-05K0-1A1C



Combination wall charger and mobile power bank charges smartphones, tablets and other mobile devices either with or without an AC outlet.

### Features

**Portable Lithium-Ion Battery Charges Your Mobile Devices at Home, on the Road...Anywhere!** Small and lightweight, this high-capacity power bank dishes out 5000mAh of battery capacity for charging two mobile devices at the same time, including smartphones, tablets, e-readers, AirPods and handheld gaming devices. Lithium-ion lasts longer than lead-acid batteries, charges faster and saves you money in the end. Status LEDs let you know how much battery capacity is left.

**Plugs Into an AC Outlet to Charge Itself and Your Mobile Devices at the Same Time** The UPBW-05K0-1A1C is a portable power bank you can take with you to charge your devices at work, on the train, at a convention or at the airport. But it also features a NEMA 1-15P plug that connects to any standard power outlet. Plugging the power bank into an AC outlet turns it into an efficient wall charger that not only charges its own battery to full capacity, but charges up to two connected mobile devices as well.

**2 USB Ports Allow You to Keep Your Phone and Other Essential Devices Ready for Use** A USB-A port and a USB-C port provide a total of 5V 2.4A (when connected to an AC outlet) or 5V 3A (DC power) to charge your devices, including Android, Apple and Windows.

**Protects Your Expensive Devices During Charging** Comprehensive safety features ensure worry-free charging of mobile devices. The power bank provides short circuit, over-voltage, over-current, over-charge and over-discharge protection.

**Compact Housing Packs in a Pocket for On-the-Go Charging** An ideal power solution when you're on the road or stuck somewhere without convenient electricity, the portable battery charger fits comfortably in your purse, pocket or backpack to keep your phone, tablet, Kindle, AirPods or other mobile device operating when you need it. The NEMA 1-15P plug folds into the unit when not in use to shield it from damage and prevent it from snagging or scratching your bag's contents.

## Specifications

### Highlights

- Plugs into wall outlet to charge up to 2 devices and itself at the same time
- Ideal for road trips, hikes, blackouts and other applications without AC power
- USB-A and USB-C ports provide up to 5V 2.4A (AC) or 5V 3A (DC) for charging
- 5000mAh of lithium-ion battery capacity is plenty for hours of maximum power draw
- LED indicators show remaining power bank battery capacity at a glance

### Applications

- Charge tablets and other mobile devices either at home or the office via AC outlet or on the go via USB charging
- Maintain your smartphones' battery capacities while camping or hiking
- Keep your mobile devices working during a utility power outage

### Package Includes

- UPBW-05K0-1A1C 5000mAh 2-Port Mobile Power Bank and USB Battery Wall Charger
- Owner's manual



<b>OVERVIEW</b>	
UPC Code	037332251725
Product Type	Portable Charger; Wall Charger
Charging Form Factor	Direct Plug-In; Portable
Device Compatibility	Phone; Tablet; Amazon Kindle
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	5V DC; 120V AC; 230V AC
Voltage Compatibility (VAC)	110; 120; 125; 127; 200; 208; 220; 230; 240
Input Plug Type	NEMA 1-15P (NON-POLARIZED)
<b>OUTPUT</b>	
Overload Protection	Yes
<b>POWER</b>	
USB Power Delivery (PD) Charging Support	No
<b>VOLTAGE REGULATION</b>	
Overvoltage Correction	Yes
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	Blue = Battery Charge Status
<b>SURGE / NOISE SUPPRESSION</b>	
Automatic Shut-Off	Yes
<b>CHARGING</b>	
Number of Charging Ports	2
Total Charging Amps	2.4A
Total Charging Watts	15
Charging Method	USB
Charging Port Type	USB A (FEMALE); USB C (FEMALE)
Charging Ports Details	(AC) USB-C: 5V/2.4A; USB-A: 5V/2.4A; Total: 5V/3A(DC) USB-C: 5V/3A; USB-A: 5V/2.4A; Total: 5V/3A
Charging Ports / Amps	2.4A; 3A
Overcharge Protection	Yes
Charging Method Detail	5,000 mAh
Boost Converter Efficiency	80%



<b>PHYSICAL</b>	
Color	Black
Material of Construction	Polycarbonate, PCB
Unit Dimensions (hwd / cm)	3.0 x 6.9 x 7.8
Unit Dimensions (hwd / in.)	1.18 x 2.72 x 3.07
Unit Dimensions (hwd / mm)	30 x 69 x 78
Unit Packaging Type	Box
Unit Weight (kg)	0.25
Unit Weight (lbs.)	0.5512
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 77°F (0° to 25°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 90% RH
Storage Humidity Range	5% to 45% RH
<b>CONNECTIONS</b>	
Side A - Connector 1	USB C (FEMALE)
Side A - Connector 2	USB A (FEMALE)
Side B - Connector 1	NEMA 1-15P (NON-POLARIZED)
<b>FEATURES &amp; SPECIFICATIONS</b>	
Over Current Protection	Yes
Driver Required	No
Quick Charge Compliant	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
GaN Technology	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to RoHS, REACH, FCC, UL
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>