

# Universal Reversible USB 2.0 Cable (Reversible A to Down-Angle 5Pin Micro B M/M), 6 ft. (1.83 m)

MODEL NUMBER: UR050-006-DNB



Universal / Reversible "A" connector allows plugging in any direction

## Features

- Universal / Reversible A connector eliminates guess-work as to connector orientation
- Down-Angle Micro B connector ideal in situations where space is at a premium, and reduces stress / excessive bending on the cable
- Available in lengths up to 10-ft.
- 480Mbps USB 2.0 Data Transfer Rates
- Data and Power transference

## Highlights

- Universal / Reversible A connector eliminates guess-work as to connector orientation
- Down-Angle Micro B connector ideal in situations where space is at a premium, and reduces stress / excessive bending on the cable
- Next Generation USB Digital Device Connector
- Provides both Data and Power transfers
- USB 2.0 480Mbps Transfer rates

## System Requirements

- Digital devices that use the USB Micro-B Female socket

## Package Includes

- 6-ft. USB2.0 Universal / Reversible A to Down-Angle Micro-USB B Device Cable (A Male to Micro-B Male)

## Specifications

OVERVIEW	
UPC Code	037332182456
Technology	USB 2.0 (High Speed)
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	REVERSIBLE USB A (MALE)
Side B - Connector 1	MICRO-USB B (MALE)
Connector Style	Angled
PHYSICAL	
Cable Jacket Color	Black
Cable Length (ft.)	6



Powering Business Worldwide



Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	0.25 x 4.70 x 9.30
Shipping Dimensions (hwd / cm)	0.64 x 11.94 x 23.62
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	14° to 122°F (-10° to 50°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	0% to 90% RH, Non-Condensing
Storage Humidity Range	0% to 90% RH, Non-Condensing
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.