

## Universal Reversible USB 2.0 Cable (Reversible A-M to 5Pin Micro B-M), 10 ft. (3.05 m)

MODEL NUMBER: UR050-010



Universal / Reversible "A" connector allows plugging in any direction

### Description

Tripp Lite UR050-010, 10-ft. (3.05 m) USB 2.0 A to Micro-B cable, features a Universal / Reversible "A" connector, which takes the guesswork out of which way to position the "A" connector for plugging. Micro-USB is the next generation of USB connector that will be found on Cell Phones, PDA's, USB On-the-Go ( OTG ) devices, Digital Cameras, and more. Smaller and more durable ( 10,000 insertion cycles ) than the existing mini-B connectors, the Micro-USB will also handle Power transfers, as well as Data. The USB Implementers Forum ( USB-IF ) has designed the Micro-USB to eliminate many of the proprietary Mini connectors found on different manufacturers digital devices, and it will be the standard USB connection on phones from the major cell phone manufacturers. USB 2.0 rated cable handles 480Mbps data transfer rates.

### Features

- USB Universal / Reversible A Male to Micro-B Male
- Available in 3-ft. (0.91 m), 6-ft. (1.83 m), and 10-ft. (3.05 m) lengths
- 480Mbps USB 2.0 Data Transfer Rates
- Data and Power transference

## Specifications

OVERVIEW	
UPC Code	037332179579
Technology	USB 2.0 (High Speed); USB

### Highlights

- Next Generation USB Digital Device Connector
- Provides both Data and Power transfers
- USB 2.0 480Mbps Transfer rates
- Universal / Reversible "A" Male to Micro-B Male

### System Requirements

- Digital devices that use the USB Micro-B Female socket

### Package Includes

- 10-ft. (3.05 m) USB2.0 Universal / Reversible A to Micro-USB B Device Cable (A Male to Micro-B Male)



<b>INPUT</b>	
Cable Length (ft.)	10
Cable Length (m)	3.1
<b>PHYSICAL</b>	
Color	Black
Shipping Dimensions (hwd / cm)	0.64 x 15.24 x 17.78
Shipping Dimensions (hwd / in.)	0.25 x 6.00 x 7.00
Shipping Weight (kg)	0.02
Shipping Weight (lbs.)	0.05
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-10/+75° C (14 to 167° F)
Storage Temperature Range	-20/+80° C (-4 to 176° F)
<b>CONNECTIONS</b>	
Side A - Connector 1	REVERSIBLE USB A (MALE)
Side B - Connector 1	MICRO-USB B (MALE)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>