

## Multimedia Remote for PCs & Laptops

MODEL NUMBER: URM-15T



### Description

The Multimedia Remote for PCs & Laptops is a RF (radio frequency) remote that allows you to control multimedia applications on your Mac or PC through walls and furniture. The remote controls your multimedia applications by sending them the same keystrokes that you do when you control the application from a keyboard.

### Features

- Sleek 17 button radio frequency remote transmits signals up to 40-ft. (12.19 m)
- Includes Windows Media Player, WinAMP, QuickTime, PowerPoint and other popular multi-media applications. Simple control panel allows you to program the remote for use with additional applications
- Perfect for earlier generations Windows OS, Vista, XP, Win7 (32 bit only)
- To locate a Win7 32 bit driver: insert receiver into USB port on your computer and a dialog box will appear asking if you want an updated Win7 32 bit driver
- Click 'yes' and follow the steps to link to the driver
- Execute the driver and reboot your computer

### Highlights

- Make multimedia software easier to control with a remote
- Ideal for presentations
- Sleek 17-key design
- 40-ft. (12.19 m) range
- Compatible with 32-bit systems only

### System Requirements

#### Mac:

- An available USB port, Mac OS 8.6-9.2.2, Mac OS X 10.2.8, Mac OS X 10.3.9 & Mac OS X 10.4.x, 10.5x & 10.6x (32 bit only)

#### Windows:

- An available USB port, Windows 98 / 98 SE / Me / 2000 / XP / Vista

#### Battery:

- Remote Control uses a CR2032 (Lithium 3V) battery (included) Note: This remote is not compatible with AirPort Express.

### Package Includes

- USB RF Receiver
- 17 button RF remote
- remote's battery (one CR2032 [Lithium 3V])
- CD with driver software and user guide
- Printed Quick Start Guide
- Carrying pouch

## Specifications

OVERVIEW	
UPC Code	672603010337
PHYSICAL	
Color	Gray; White
Shipping Dimensions (hwd / in.)	2.40 x 8.10 x 6.70
Shipping Dimensions (hwd / cm)	6.10 x 20.57 x 17.02

Shipping Weight (lbs.)	0.30
Shipping Weight (kg)	0.14
COMMUNICATIONS	
Signal Range (ft.)	40
Signal Range (m)	12
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.