

WorkWise Standing Desk Base, Electric Adjustable-Height, Gray

MODEL NUMBER: WWBASE-GY



Electric adjustable-height desk base attaches to a desk top (sold separately) to create a more ergonomic workspace that accommodates sitting, standing and the comfort of different users.

Description

Tripp Lite's WWBASE-GY WorkWise™ Standing Desk Base lets you change the height of your workspace at the touch of a button. The DC linear actuator motor lifts or lowers a desk top at a speed of 1.5 inches per second. Base height adjusts from 23.5 to 49 inches in precise 0.1-inch increments for standing and sitting positions perfectly customized for your comfort.

The included control handset mounts beneath a desk top and connects to the motor. It features buttons for up/down movement and a digital readout that displays height in inches. You can create up to four convenient preset positions, making it easy to instantly adjust the WWBASE-GY to the perfect height for you, as well as the officemate who shares your workspace. You can also set upper and lower limits if you prefer a narrower range of heights.

The WWBASE-GY is made of steel with a gray powder-coated finish. You can adjust its width between 42.5 and 72 inches to accommodate a variety of desk tops (sold separately). It perfectly matches the threaded mounting inserts on Tripp Lite WorkWise Desk Tops, including WWTOP48-BK, WWTOP48-ES, WWTOP60-BKC, WWTOP60-ESC, WWTOP60-WHC, WWTOP72-BK and WWTOP72-ES. Pre-installed leveling feet keep it stable on uneven floors. Includes a 10-ft. (3.05 m) power cord with two-prong plug that connects to a 120V AC outlet. Meets ANSI/BIFMA X5.5-2014 standards. Maximum load capacity of 365 lbs (165.6 kgs.). Assembles in less than 30 minutes.

Features

Precise Electric Height Adjustment

- Height adjusts in precise 0.1 in. increments from 23.5 to 49 in.
- Powerful DC linear actuator motor moves base legs 1.5 in. per second

Highlights

- Steel construction with gray powder-coated finish
- Height adjusts in precise 0.1 in. increments from 23.5 to 49 in.
- Width adjusts to fit all WorkWise Desk Tops (sold separately)
- Create up to 4 convenient preset positions
- Electric motor adjusts height 1.5 in. per second

Package Includes

WWBASE-GY (Base Only)

- Control box
- Handset
- (2) Legs
- (2) Feet
- (2) Frame ends
- (2) Center rails
- (2) Side brackets
- (8) M6 x 10 screws
- (16) M6 x 14 screws
- (4) M6 x 35 screws
- (7) M5 x 20 wood screws
- (2) M5 x 16 wood screws
- (10) Cable clips
- Hex key, 4 mm
- AC power cord w/NEMA 1-15 plug, 10-ft. (3.05 m)
- Male-to-female extension cable, 4.3-ft. (1.31 m)
- Owner's manual



- Create up to 4 convenient preset positions for one-touch adjustment
- Set programmable upper and lower height limits
- 10-ft. (3.05 m) power cord with two-prong plug connects to 120V AC outlet

Control Handset

- Digital readout displays height in inches
- Up/down buttons adjust height with just a touch
- Mounts beneath desk top

Width Adjusts to Fit a Variety of Desk Tops (Sold Separately)

- Width adjusts from 42.5 to 72 in.
- Base perfectly matches threaded mounting inserts on Tripp Lite WorkWise Desk Tops, including WWTOP48-BK, WWTOP48-ES, WWTOP60-BKC, WWTOP60-ESC, WWTOP60-WHC, WWTOP72-BK and WWTOP72-ES

Durable Construction

- Made of steel with a gray powder-coated finish
- Pre-installed leveling feet for stability on uneven floors
- Meets ANSI/BIFMA X5.5-2014 standards
- Maximum load capacity of 365 lbs (165.6 kgs)
- Assembles in less than 30 min.

Specifications

OVERVIEW	
UPC Code	037332196873
INPUT	
Voltage Compatibility (VAC)	120
Input Frequency	60 Hz
PHYSICAL	
Color	Gray
Maximum Weight Capacity (kg)	166
Maximum Weight Capacity (lbs.)	365
Shipping Dimensions (hwd / cm)	104.14 x 24.38 x 25.40
Shipping Dimensions (hwd / in.)	41.00 x 9.60 x 10.00
Shipping Weight (kg)	29.94



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Shipping Weight (lbs.)	66.00
Standing Desk Base Color	Gray
Unit Dimensions (hwd / cm)	59.69-124.46 x 107.95-182.88 x 57.51
Unit Dimensions (hwd / in.)	23.5-49 x 42.5-72 x 22.64
Unit Weight (kg)	24.95
Unit Weight (lbs.)	55
STANDARDS & COMPLIANCE	
Certifications	UL 1004-7, UL 1004-1, UL 508:1999, CSA C22.2 100-04, CSA C22.2 77-95, CSA C22.2 14-10
Approvals	ANSI/BIFMA X5.5-2014
WARRANTY	
Product Warranty Period (U.S. & Canada)	5-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>