

PDU Power Cord, C13 to C14 - 10A, 250V, H05VV-F, 1 m (3.3 ft.), Black

MODEL NUMBER: P004-01M-EU



Extension cord connects 2 devices with C13/C14 power connectors or extends your existing power connection by 1 m.

Features

C13-to-C14 Power Cord Connects Computers, Printers, Servers and Other Equipment

This durable extension cord is designed for small data centers, office workstations and other lower-amp applications. The power cable can be used to power a computer, server or monitor or to attach a server or drive to a PDU. It can also extend an existing connection up to one meter (3.3 feet) to right-size your current application and allow some flexibility in placing connected equipment.

H05VV-F Jacket Is Fully VDE-Compatible for European Applications

The 0.75mm² enhanced PVC jacket complies with VDE, CE and UKCA standards for data centers, racks and other IT applications in Europe.

Highlights

- Connects a PC or server to a PDU or UPS system in a data rack or cabinet
- Adds 1 m to your existing power connection to provide flexibility in placing devices
- Fully VDE-compatible for European IT applications
- Ideal replacement for worn-out or missing power cable

Package Includes

P004-01M-EU C13 to C14 Power Cord, 1 m (3.3 ft.), Black

Specifications

OVERVIEW	
UPC Code	037332280879
Product Type	PDU Extension Power Cord
Device Compatibility	Computer; PDU; Server
Country/Region	Europe
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	250
CONNECTIONS	
Side A - Connector 1	IEC-320-C13



Powering Business Worldwide

TRIPP LITE
SERIES

Side B - Connector 1	IEC-320-C14
Connector Style	Straight
PHYSICAL	
Color	Black
Plug Color	Black
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Power Cord Jacket Type	H05VV-F
Cable Outer Diameter (OD)	6.7 mm
Number of Conductors	3
Conductor Gauge	24/0.20AS
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.75
Power Cord Color	Black
Cable Length (ft.)	3.3
Cable Length (m)	1.01
Cable Length (cm)	100
Shipping Dimensions (hwd / in.)	9.02 x 7.01 x 0.50
Shipping Dimensions (hwd / cm)	22.91 x 17.81 x 1.27
Shipping Weight (lbs.)	0.25
Shipping Weight (kg)	0.11
Unit Dimensions (hwd / in.)	9.020 x 7.010 x 0.500
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.24
Unit Weight (kg)	0.11
ENVIRONMENTAL	
Operating Temperature Range	5° to 158° F (-15° to 70°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	20% TO 80% RH, NON-CONDENSING
Storage Humidity Range	20% TO 80% RH, NON-CONDENSING
FEATURES & SPECIFICATIONS	
Antibacterial	No
Armored Cable	No



Powering Business Worldwide

TRIPP LITE
SERIES

Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
Locking Power Cord	No
Locking	No
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.