

EU Computer Power Cord, Schuko to C19 - 16A, 250V, H05VV-F, 2.5 m (8.2 ft.), Black

MODEL NUMBER: P050-2P5M-EU



Connects a server or PC with a C20 plug to a PDU or UPS with Schuko outlets.

Features

EU Power Cord Connects Data Center Equipment to Reliable AC Power

This VDE-compliant power cable connects a computer, server, hard drive or other device with a C20 plug to a PDU, UPS system or surge protector with Schuko outlets. It can also extend an existing power connection up to 2.5 meters (8.2 feet). The P050-2P5M-EU features a CEE 7/7 Schuko end for connecting to an AC power source and an IEC-320-C19 end for connecting to a network device in a data center or other IT application.

H05VV-F Jacket Is Fully VDE-Compatible for European Applications

The 0.75mm² enhanced PVC jacket complies with VDE, CE and UKCA standards for data centers, racks, workstations and other IT applications in Europe.

Highlights

- Recommended for powering computers, servers, drives and other network devices
- 2.5-meter length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for a worn-out or missing power cord
- VDE-compliant H05VV-F jacket allows use in European IT applications

Applications

- Connect devices like computers, servers and drives to a PDU up to 2.4 m away in your data center
- Transform a C20 plug into a Schuko plug with no electrician needed
- Extend an existing power connection up to 2.4 m to more easily place a device or reach a power source in a rack
- Provide a high-quality replacement for a worn-out or missing power cord

Package Includes

P050-2P5M-EU C19 to Schuko EU Power Cable, 2.5 m (8.2 ft.), Black

Specifications

OVERVIEW	
UPC Code	037332281234
Product Type	Computer Power Cord
Device Compatibility	Computer
Country/Region	Europe
INPUT	
Maximum Input Amps	16
Voltage Compatibility (VAC)	250
CONNECTIONS	
Side A - Connector 1	CEE 7/7 SCHUKO PLUG



Powering Business Worldwide

TRIPP LITE
SERIES

Side B - Connector 1	IEC-320-C19
Connector Style	Straight
PHYSICAL	
Color	Black
Plug Color	Black
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Power Cord Jacket Type	H05VV-F
Cable Outer Diameter (OD)	7.0 mm
Number of Conductors	3
Conductor Gauge	32/0.20AS
Wire Gauge (AWG)	17
Wire Gauge (OD - mm ²)	1
Power Cord Color	Black
Cable Length (ft.)	8.2
Cable Length (m)	2.50
Shipping Dimensions (hwd / in.)	10.00 x 7.99 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 20.29 x 1.27
Shipping Weight (lbs.)	0.64
Shipping Weight (kg)	0.29
Unit Dimensions (hwd / in.)	10.000 x 7.990 x 0.500
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.62
Unit Weight (kg)	0.28
ENVIRONMENTAL	
Operating Temperature Range	5° to 158°F (-15° to 70°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	20% TO 80% RH, NON-CONDENSING
Storage Humidity Range	20% TO 80% RH, NON-CONDENSING
FEATURES & SPECIFICATIONS	
Antibacterial	No
Armored Cable	No
Angled Plug	No



Powering Business Worldwide

TRIPP LITE
SERIES

High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
Locking Power Cord	No
Locking	No
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.