

PDU Power Cord, Schuko to C13 - 10A, 100-250V, H05VV-F, 2 m (6.6 ft.), Black

MODEL NUMBER: P054-02M-EU



Connects a computer, server or drive with a C14 plug to a Schuko wall outlet.

Features

Power Cord Connects Data Center Equipment to Reliable AC Power

This VDE-compliant power cable connects a computer, server or drive with a C14 plug to a PDU, UPS or surge protector with Schuko outlets. Or you can extend an existing power connection up to two meters (6.6 feet). The P054-02M-EU features a CEE 7/7 Schuko end for connecting to an AC power source and an IEC-320-C13 end for connecting to a network device in a data center or other IT application.

H05VV-F Jacket Is Fully VDE-Compatible for European Applications

The 0.75mm² enhanced PVC jacket complies with VDE, CE and UKCA standards for data centers, racks, workstations and other IT applications in Europe.

Highlights

- 2-meter length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for a worn-out or missing power cord
- VDE-compliant H05VV-F jacket allows use in European IT applications

Package Includes

P054-02M-EU C13 to Schuko PDU Power Cable, 2 m (6.6 ft.), Black

Specifications

OVERVIEW	
UPC Code	037332280916
Product Type	PDU Extension Power Cord
Device Compatibility	Computer; PDU; Server
Country/Region	Europe
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	250
CONNECTIONS	
Side A - Connector 1	CEE 7/7 SCHUKO PLUG



Powering Business Worldwide

TRIPP LITE
SERIES

Side B - Connector 1	IEC-320-C13
Connector Style	Straight
PHYSICAL	
Color	Black
Plug Color	Black
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Power Cord Jacket Type	H05VV-F
Cable Outer Diameter (OD)	6.7 mm
Number of Conductors	3
Conductor Gauge	24/0.20AS
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.75
Power Cord Color	Black
Cable Length (ft.)	6.56
Cable Length (m)	2.00
Cable Length (cm)	100
Shipping Dimensions (hwd / in.)	9.02 x 7.01 x 0.50
Shipping Dimensions (hwd / cm)	22.91 x 17.81 x 1.27
Shipping Weight (lbs.)	0.43
Shipping Weight (kg)	0.20
Unit Dimensions (hwd / in.)	9.020 x 7.010 x 0.500
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.24
Unit Weight (kg)	0.11
ENVIRONMENTAL	
Operating Temperature Range	5° to 158° F (-15° to 70° C)
Storage Temperature Range	5° to 140° F (-15° to 60° C)
Operating Humidity Range	20% TO 80% RH, NON-CONDENSING
Storage Humidity Range	20% TO 80% RH, NON-CONDENSING
FEATURES & SPECIFICATIONS	
Antibacterial	No
Armored Cable	No



Powering Business Worldwide

TRIPP LITE
SERIES

Angled Plug	No
High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
Locking Power Cord	No
Locking	No
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.