

Laptop Power Cord, Schuko to C5 - 2.5A, 250V, H05VV-F, 2 m (6.6 ft.), Black

MODEL NUMBER: P058-02M-EU



Connects a notebook computer or laptop with a 3-slot C6 power inlet to a PDU or UPS system with Schuko outlets.

Features

European Computer Power Cord Connects Notebook Computers to a Schuko AC Outlet

This VDE-compliant power cable connects a notebook computer, laptop or other device with a three-slot C6 inlet to a PDU, UPS or surge protector with Schuko outlets. The P058-02M-EU features a CEE 7/7 Schuko end for connecting to an AC power source and an IEC-320-C5 end for connecting to devices.

H05VV-F Jacket Is Fully VDE-Compatible for European Applications

The 0.75mm2 enhanced PVC jacket complies with VDE, CE and UKCA standards for data centers, racks, workstations and other IT applications in Europe.

Highlights

- Recommended for powering notebook computers and laptops with C6 inlets
- Ideal replacement for a worn-out or missing laptop adapter power cable
- VDE-compliant H05VV-F jacket allows use in European IT applications

Package Includes

P058-02M-EU C5 to Schuko Computer Power Cable, 2 m (6.6 ft.), Black

Specifications

OVERVIEW	
UPC Code	037332281074
Product Type	Computer Power Cord
Device Compatibility	Laptop; Monitor/HDTV
Country/Region	Europe
INPUT	
Maximum Input Amps	2.5
Voltage Compatibility (VAC)	250
CONNECTIONS	
Side A - Connector 1	CEE 7/7 SCHUKO PLUG



Powering Business Worldwide

TRIPP LITE
SERIES

Side B - Connector 1	IEC-320-C5
Connector Style	Straight
PHYSICAL	
Color	Black
Plug Color	Black
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Power Cord Jacket Type	H03VV-F
Cable Outer Diameter (OD)	5.9 mm
Number of Conductors	3
Conductor Gauge	24/0.20AS
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	0.75
Power Cord Color	Black
Cable Length (ft.)	6.56
Cable Length (m)	2.00
Shipping Dimensions (hwd / in.)	9.02 x 7.01 x 0.50
Shipping Dimensions (hwd / cm)	22.91 x 17.81 x 1.27
Shipping Weight (lbs.)	0.37
Shipping Weight (kg)	0.17
Unit Dimensions (hwd / in.)	9.020 x 7.010 x 0.500
Unit Packaging Type	Polybag
Unit Weight (lbs.)	0.36
Unit Weight (kg)	0.16
ENVIRONMENTAL	
Operating Temperature Range	5° to 158°F (-15° to 70°C)
Storage Temperature Range	5° to 140°F (-15° to 60°C)
Operating Humidity Range	20% TO 80% RH, NON-CONDENSING
Storage Humidity Range	20% TO 80% RH, NON-CONDENSING
FEATURES & SPECIFICATIONS	
Antibacterial	No
Armored Cable	No
Angled Plug	No



Powering Business Worldwide

TRIPP LITE
SERIES

High Voltage	Yes
Locking Plug	No
Coiled Power Cord	No
Locking Power Cord	No
Locking	No
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); REACH; RoHS; UKCA
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.