

## DisplayPort Cable with Latching Connectors, 4K 60 Hz (M/M), Black, 6 ft. (1.83 m)

MODEL NUMBER: P580-006



### Highlights

- Digital Video and Audio in one cable
- Displayport Monitor Cable with Latches (M/M) 6-ft. (1.83 m)
- Small footprint compared to VGA or DVI
- Supports Ultra High Definition (UHD) 4K x 2K video resolutions up to 3840 x 2160 @ 60Hz, including 1080p

### Package Includes

- Displayport Monitor Cable with Latches (M/M) 6-ft. (1.83 m)

### Features

- The future standard for Digital Video and Audio connections
- Displayport Monitor Cable with Latches (M/M) 6-ft. (1.83 m)
- Supports Displayport v1.2
- Supports High Definition Content Protection (HDCP)
- Supports Ultra High Definition (UHD) 4K x 2K video resolutions up to 3840 x 2160 @ 60Hz, including 1080p

## Specifications

| OVERVIEW                       |                         |
|--------------------------------|-------------------------|
| UPC Code                       | 037332145963            |
| Product Type                   | Passive Cable           |
| Technology                     | DisplayPort             |
| Cable Type                     | Passive                 |
| VIDEO                          |                         |
| Max Supported Video Resolution | 3840 x 2160 (4K) @ 60Hz |
| Max Supported Color Depth      | 24-bit True Color       |
| HDR Support                    | No                      |
| 3D Video Supported             | Yes                     |
| Chroma Sub Sampling            | 4:2:0; 4:2:2            |
| Signal Transmission            | Bidirectional           |



Powering Business Worldwide

TRIPP LITE  
SERIES

| CONNECTIONS                                  |                               |
|----------------------------------------------|-------------------------------|
| Side A - Connector 1                         | DISPLAYPORT (MALE)            |
| Side B - Connector 1                         | DISPLAYPORT (MALE)            |
| Connector Plating                            | Nickel                        |
| Contact Plating                              | Gold                          |
| Connector Style                              | Straight                      |
| Latching or Gripping Connector               | Yes                           |
| PHYSICAL                                     |                               |
| Color                                        | Black                         |
| Cable Jacket Color                           | Black                         |
| Cable Jacket Material                        | PVC                           |
| Cable Jacket Rating                          | VW-1                          |
| Cable Outer Diameter (OD)                    | 6.0 mm                        |
| Wire Gauge (AWG)                             | 30                            |
| Cable Length (ft.)                           | 6                             |
| Cable Length (m)                             | 1.83                          |
| Cable Length (in.)                           | 72                            |
| Ferrite Core                                 | No                            |
| Minimum Bend Radius                          | 60mm                          |
| Shipping Dimensions (hwd / in.)              | 9.00 x 7.00 x 0.50            |
| Shipping Dimensions (hwd / cm)               | 22.86 x 17.78 x 1.27          |
| Shipping Weight (lbs.)                       | 0.25                          |
| Shipping Weight (kg)                         | 0.11                          |
| ENVIRONMENTAL                                |                               |
| Operating Temperature Range                  | 32° to 113°F (0° to 45°C)     |
| Storage Temperature Range                    | -40° to 158°F (-40° to 70°C)  |
| Operating Humidity Range                     | 10% to 85% RH, Non-Condensing |
| Storage Humidity Range                       | 5% to 90% RH, Non-Condensing  |
| COMMUNICATIONS                               |                               |
| EDID Compatible                              | Yes                           |
| Consumer Electronics Control (CEC) Supported | No                            |
| FEATURES & SPECIFICATIONS                    |                               |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                     |                           |
|-------------------------------------|---------------------------|
| EMI/RFI Line Noise Protection       | No                        |
| MST Support                         | Yes                       |
| Antibacterial                       | No                        |
| IP68 Rated                          | No                        |
| Armored Cable                       | No                        |
| Ethernet Support                    | No                        |
| Displayport Specification           | 1.2                       |
| HDCP Specification                  | 2.2                       |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                           |
| Product Compliance                  | RoHS; REACH; WEEE         |
| <b>WARRANTY &amp; SUPPORT</b>       |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.