

SmartRack 12U Low-Profile Switch-Depth-Plus Wall-Mount Small Rack Enclosure

MODEL NUMBER: SRW12UDP



Wall-mount cabinet secures and organizes 12U of 19-inch rack equipment in network closets, classrooms and other locations with limited floor space. Houses network switches and patch panels up to 20.5 inches deep.

Description

The SRW12UDP SmartRack® 12U Low-Profile Switch-Depth-Plus Wall-Mount Rack Enclosure Cabinet is designed to house EIA-standard 19-inch rack equipment in network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way. Constructed from heavy-duty steel with a durable black powder-coated finish, the cabinet has a maximum load capacity of 200 pounds (90.7 kilograms).

To ensure your valuable equipment stays secure, the side panels and front door lock securely to help prevent damage, tampering or theft. The front, top, bottom and removable side panels are vented, which allows air to flow freely through the cabinet to keep equipment cool. The reversible front door can open left or right by rotating the cabinet 180° before mounting. Convenient top and bottom ports allow easy cable routing through the cabinet.

The SRW12UDP comes fully assembled and ready to mount to the wall, or use an optional SRCASTER rolling caster kit to make it a mobile rack. Square and threaded mounting holes and numbered rack spaces make equipment installation easy. The vertical mounting rails adjust in 7/8-inch increments to accommodate equipment up to 20.5 inches deep, such as network switches and patch panels.

Features

Saves Valuable Workspace

- Perfect for network wiring closets, retail locations, classrooms, back offices and other areas with limited floor space where you need equipment to be secure, organized and out of the way
- Houses EIA-standard 19 in. rack equipment in 12U of space
- Maximum load capacity of 200 pounds (90.7 kg)

Keeps Important Equipment Secure

- Side panels and front door lock securely to help prevent damage, tampering or theft
- Vented panels allow generous airflow that keeps equipment cool
- Rotate cabinet 180° before mounting to open reversible front door left or right
- Convenient ports with removable covers allow cable routing through top and bottom

Easy Enclosure and Equipment Installation

Highlights

- Maximum load capacity of 200 lbs (90.7 kgs)
- Locking steel cabinet vented at sides, front, top and bottom
- Flow-through ventilation keeps equipment cool
- Secures 12U of 19 in. rack equipment up to 20.5 in. deep
- Mounts to wall or rolls on floor (with optional SRCASTER)

Package Includes

- SRW12UDP SmartRack 12U Low-Profile Switch-Depth-Plus Wall-Mount Rack Enclosure Cabinet
- (20) M6 screws
- (20) M6 cage nuts
- (20) M6 washers
- (20) 12-24 screws
- (2) Keys
- Owner's manual



Powering Business Worldwide



- Ships fully assembled for quick installation
- Mounts to wall or rolls on floor with optional SRCASTER caster kit
- Wall-mounting holes spaced 16 in. apart for standard wall stud placement
- Vertical mounting rails adjust in 7/8 in. increments to accommodate equipment up to 20.5 in. deep, such as network switches and patch panels
- Rails support square-hole or 12-24 threaded-hole mounting
- Rack spaces numbered for easy reference

Meets Payment Card Industry Standards

- Provides physical equipment and media security required for PCI DSS (Payment Card Industry Data Security Standard) compliance

Specifications

OVERVIEW	
UPC Code	037332191472
Device Compatibility	Patch Panel; Network Switch; UPS
Rack Type	Small Enclosure
PHYSICAL	
Color	Black
Rack Height	12U
Rack Depth	Shallow
Maximum Device Depth (cm)	52.07
Maximum Device Depth (in.)	20.5
Maximum Device Depth (mm)	521
Minimum Device Depth (cm)	7.62
Minimum Device Depth (in.)	3
Minimum Device Depth (mm)	76
Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
Shipping Dimensions (hwd / in.)	29.72 x 28.75 x 26.57
Shipping Dimensions (hwd / cm)	75.49 x 73.02 x 67.49
Shipping Weight (lbs.)	57.00
Shipping Weight (kg)	25.85
Unit Dimensions (hwd / in.)	25.080 x 23.620 x 21.750
Unit Dimensions (hwd / cm)	63,70 x 60,00 x 55,25
Unit Weight (lbs.)	58.4
Unit Weight (kg)	26.49



Powering Business Worldwide



Weight Capacity - Stationary (kg)	91
Weight Capacity - Stationary (lbs.)	200
Number of Vertical Mounting Rails	4
FEATURES & SPECIFICATIONS	
Grounding Details	Front and Back door frames
Pre-Installed Casters	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.