SR25UBTAA

SmartRack® TAA-Compliant Rack Enclosure



















Depth Index Requirements



Integrated **Baying Tabs**




Square Hole Mounting

- 25 Rack Units
- 3000 lb Stationary **Load Capacity**
 - Rolling **Load Capacity**
- 2250 lb
- Rolling Casters
- Locking Doors & **Side Panels**
 - Standard
 - 19-inch Rack Width
- Toolless **Mounting Slots**
- Adjustable Rails with Easy-View
- Airflow Exceeds Server OEM

- A Adjustable Mounting Rails (4)
- **B** Adjustable PDU Mounting **Rails with Toolless Mounting Slots** (2 rails hold up to 4 vertical PDUs.)
- C Roof Panel (Removable)
- Front Door (Lockable/Removable/Reversible)
- Split Rear Doors (2) (Lockable/Removable)
- Side Panels (2) (Lockable/Removable)
- G Rolling Casters (4)
- H Levelers (4)
- (For doors and side panels.)

Also Includes: Owner's manual, 2 shipping/stabilizing brackets and rackmount equipment mounting hardware (50 cage nuts, 50 mounting screws, 50 nylon cup washers).

















- **Specifications** Model SR25UBTAA **Rack Spaces** Stationary Load Capacity 3000 lb (1361 kg) **Rolling Load Capacity** 2250 lb (1021 kg) Unit Dimensions (H x W x D) 49 x 23.63 x 43 in (1245 x 600 x 1092 mm) Shipping Dimensions (H x W x D) 55 x 26 x 45 in (1397 x 660 x 1143 mm) Unit Weight 195 lb (88.5 kg) Shipping Weight 237 lb (107.5 kg) Certifications Tested to UL/EN 60950-1, CSA (Canada), NOM (Mexico), EIA/ECA-310-E, IEC 60297-3-100, DIN 41494, IP20, RoHS, PCI-DSS, TAA Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.
- · Enclosures ship fully assembled for rapid deployment, but can be knocked down for easy reassembly in confined spaces
- · Modular design optimized for quick configuration and reconfiguration
- · Ideal for rackmount server, network and telecom applications


SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS




1111 W. 35th Street Chicago, IL 60609 USA 773.869.1234 www.tripplite.com

























SR25UBTAA

TRIPP-LITE

1111 W. 35th Street Chicago, IL 60609 USA 773.869.1234 www.tripplite.com

Dimensions: [mm] INCHES

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.