SR42UBTAA

SmartRack® TAA-Compliant Rack Enclosure



42 Rack Units 3000 lb



Stationary

2250 lb Rolling Load Capacity Load Capacity



Rolling Casters



Locking Doors & **Side Panels**



Standard 19-inch Rack Width



Toolless **Mounting Slots**



Adjustable Rails with Easy-View Depth Index



Exceeds Server OEM Requirements




Integrated **Baying Tabs**



Square Hole Mounting

- A Adjustable Mounting Rails (4)
- **B** Adjustable PDU Mounting **Rails with Toolless Mounting Slots** (2 rails hold up to 4 vertical PDUs.)
- C Roof Panel (Removable)
- Front Door (Lockable/Removable/Reversible)
- E Split Rear Doors (2) (Lockable/Removable)
- Side Panels (4) (Lockable/Removable)
- G Rolling Casters (4)
- H Levelers (4)
- (For doors and side panels.)

Also Includes: Owner's manual, 2 shipping/stabilizing brackets and rackmount equipment mounting hardware (50 cage nuts, 50 mounting screws, 50 nylon cup washers).
















Model	SR42UBTAA
Rack Spaces	42U
Stationary Load Capacity	3000 lb (1361 kg)
Rolling Load Capacity	2250 lb (1021 kg)
Unit Dimensions (H x W x D)	78.5 x 23.63 x 43 in (1994 x 600 x 1092 mm)
Shipping Dimensions (H x W x D)	84.5 x 27.75 x 47 in (2146 x 705 x 1194 mm)
Unit Weight	286 lb (129.7 kg)
Shipping Weight	304 lb (137.9 kg)
Certifications	Tested to UL/EN 60950-1, CSA (Canada),
	NOM (Mexico), EIA/ECA-310-E, IEC 60297-3-100 DIN 41494, IP20, RoHS, PCI-DSS, TAA


- · Enclosures ship fully assembled for rapid deployment, but can be knocked down for easy reassembly in confined spaces
- · Modular design optimized for quick configuration and reconfiguration
- Ideal for rackmount server, network and telecom applications


SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS





1111 W. 35th Street Chicago, IL 60609 USA 773.869.1234 www.tripplite.com














MODEL:
SR42UBTAA



1111 W. 35th Street Chicago, IL 60609 USA 773.869.1234 www.tripplite.com

Dimensions: [mm] INCHES

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.