

MODEL:

PDU3EVN10G60B

3-Phase Monitored 0U Vertical PDU



200/208/240V
3-Phase Input



60A Blue
IEC 309 3P+E
Plug



200/208/240V
Single-Phase
Output



48 Total
Outlets



14.5kW Load
Capacity



Touchscreen
LCD



Network
Interface






0U
Rackmount







Toolless
Mounting
Buttons

- A** Color Touchscreen LCD
- B** C13 and C19 Outlets with Multi-Function LEDs
- C** 20A 2-Pole Hydraulic Magnetic Circuit Breakers
- D** C13 and C19 Plug Inserts
- E** Removable Mounting Brackets
- F** Toolless Mounting Buttons with Removable 90° Rotation Brackets
- G** 10 ft. Input Power Cord
- H** 60A Blue IEC 309 3P +E Input Plug (IP44)
- I** LX Platform Interface
- J** USB-B Port (for Direct Console Access)
- K** USB-A Ports (for EnviroSense2 Sensors)
- L** RJ45 Configuration Port
- M** Ethernet Port
- N** Network Interface Reset Button

Color Touchscreen LCD:
Easily toggle between menus to monitor input current level per phase, output current per load bank, environmental sensor data and network information. It also generates a unique QR code to allow access to the monitored PDU through a mobile device.



LX Platform Interface: Connect to 10/100/1000 Mbps Ethernet networks for remote monitoring via SNMP, Web, SSH, or Telnet.
*Add optional EnviroSense2 (E2) modules for temperature, humidity, and dry contact signaling.



Note: Installed 17.67 mm toolless mounting buttons can be replaced with included 14.17 mm buttons for additional compatibility.

- Distributes power to 48 outlets (14 C13 and 2 C19 per phase)
- Java-free, HTML5-based network interface allows for remote monitoring via SNMP, Web, SSH or Telnet
- Displays load for any output phase in real time
- Perfect for rack-mount server, network and telecom applications

SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS








1111 W. 35th Street
Chicago, IL 60609 USA
773.869.1234
www.tripplite.com

Specifications

Model	PDU3EVN10G60B
Voltage	200/208/240V (3-Phase Input, Single-Phase Output)
Frequency	50/60 Hz
Load Capacity	12.1kW (200V), 12.6kW (208V), 14.5kW (240V)
Input Connector	60A Blue IEC 309 3P+E
Cord Length	10 ft. / 3 m
Outlets	48 (42 C13 / 6 C19)
Primary Mounting Option	0U (Vertical) Rack-mount
Unit Dimensions	70 x 2.17 x 2.86 in. / 1778 x 55 x 73 mm
Unit Weight	18.7 lb. / 8.5 kg
Standards	Tested to UL 60950-1 (US & Canada), NOM (Mexico), FCC Class A; RoHS; TAA





Dimensions: [mm] INCHES

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

MODEL:
PDU3EVN10G60B

TRIPP-LITE

1111 W. 35th Street
Chicago, IL 60609 USA
773.869.1234
www.triplite.com