MODEL:

PDU3EVSR6H50

3-Phase Switched 0U Vertical PDU

200/208/240V 3-Phase Input | **50A HUBBELL CS8365C Plug** | **200/208/240V Single-Phase Output** | **30 Outlets** | **14.5kW Load Capacity** | **Touchscreen LCD** | **HTML5 Network Interface** | **0U Rackmount** | **Toolless Mounting Buttons**

- A Color Touchscreen LCD
- B C13 and C19 Outlets with Multi-Function LEDs
- C 20A 2-Pole Hydraulic Magnetic Circuit Breakers
- D C13 and C19 Plug-Lock Inserts
- E Removable Mounting Brackets
- F Toolless Mounting Buttons with Removable 90° Rotation Brackets
- G 6 ft. Input Power Cord
- H 50A Hubbell CS8365C Input Plug
- I LX Platform Interface
- J USB-B Port (for Direct Console Access)
- K USB-A Ports (for EnviroSense2 Sensors)
- L RJ45 Configuration Port
- M Ethernet Port
- N Network Interface Reset Button

Not Shown: Configuration Cable, Owner's Manual

AC Input Connection: Insert 50A HUBBELL CS8365C plug into compatible utility, generator or UPS outlet.

Color Touchscreen LCD: Easily toggle between menus to monitor input current level per phase, output current per load bank and per outlet, environmental sensor data and network information. It also generates a unique QR code to allow access to the switchable PDU through a mobile device.



LX Platform Interface: Connect to Ethernet for remote monitoring and individual outlet control via SNMP, Web, SSH or telnet.

*Add optional EnviroSense2 (E2) modules for temperature/humidity monitoring and dry contact interface.

Note: Installed 17.67 mm toolless mounting buttons can be replaced with included 14.17 mm buttons for additional compatibility.

- Distributes power to 30 outlets (8 C13 & 2 C19 per bank)
- Java-free, HTML5-based network interface allows for remote monitoring and control via SNMP, Web, SSH or telnet
- Reports current for each **phase, bank, and outlet** in real-time
- Perfect for rack-mount server, network and telecom applications

SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS

Specifications

Model	PDU3EVSR6H50
Voltage	200/208/240V (3-Phase Input, Single-Phase Output)
Frequency	50/60 Hz
Load Capacity	12.1kW (200V), 12.6kW (208V), 14.5kW (240V)
Input Connector	50A Hubbell CS8365C Input Plug
Cord Length	6 ft. / 1.8 m
Outlets	30 (24 C13 / 6 C19)
Primary Mounting Option	0U (Vertical) Rack Mount
Unit Dimensions	70 x 2.17 x 2.86 in. / 1778 x 551 x 726 mm
Unit Weight	20 lb. / 9 kg
Standards	Tested to UL 60950-1 (US & Canada), NOM (Mexico), FCC Class A; RoHS; TAA

1111 W. 35th Street
Chicago, IL 60609 USA
773.869.1234
www.tripplite.com













MODEL:
PDU3EVSR6H50

TRIPP·LITE

1111 W. 35th Street
Chicago, IL 60609 USA
773.869.1234
www.tripplite.com

Dimensions: [mm] INCHES

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Copyright © 2017 Tripp Lite.