

MODEL:

PDUMH20NET2LX

Single-Phase Switched 1U Rack-Mount PDU



100/120/127V
Single-Phase
Input/Output



8 Outlets
(5-15/20R)



1.9kW Load
Capacity




16A Max
Capacity



L5-20P Plug



Digital
Load Meter



Network
Interface





1U
Rackmount



TAA
Compliant

- A** Digital Load Meter
- B** NEMA 5-15/20R Outlets
- C** Removable Mounting Brackets
- D** 12 ft. Input Power Cord
- E** NEMA L5-20P Twist-Lock Input Plug
- F** Durable Metal Case
- G** LX Platform Interface
- H** RJ45 Ethernet Port
- I** RJ45 Configuration Port
- J** USB-A Port
- K** Reset Button
- L** Status LED
- M** Removable Cord Retention Bracket

Also Includes:
Configuration Cable,
Cable Ties,
Owner's Manual



AC Input Connection: Insert L5-20P twist-lock plug into compatible L5-20R utility, generator or UPS outlet.

LX Platform Interface: Connect to Ethernet for remote monitoring and individual outlet control via SNMP, Web, SSH or telnet. Add optional EnviroSense2 (E2) modules for temperature/humidity monitoring and dry contact interface.

- Distributes power to 8 outlets
- Java-free HTML5-based network interface allows for remote monitoring and control via SNMP, Web, SSH or telnet
- Displays total PDU load in real time
- Recommended for rack-mount server, network and telecom applications


SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS

Specifications


Model	PDUMH20NET2LX
Voltage	100/120/127V
Frequency	50/60 Hz
Load Capacity	2.0kW (127V), 1.9kW (120V), 1.6kW (100V)
Input Connector	L5-20P
Cord Length	12 ft. / 3.65 m
Outlets	8 (5-15/20R)
Primary Mounting Option	1U Rack Mount
Unit Dimensions (H x W x D)	1.75 x 17.5 x 4.25 in. / 4.44 x 44.4 x 10.8 cm
Unit Weight	6 lb. / 2.7 kg
Standards	Tested to UL 60950-1 (U.S. & Canada), NOM (Mexico), RoHS, TAA




1111 W. 35th Street
Chicago, IL 60609 USA
773.869.1234
www.tripplite.com




FRONT VIEW



TOP VIEW



BACK VIEW



SIDE VIEW

MODEL:
PDUMH20NET2LX



1111 W. 35th Street
Chicago, IL 60609 USA
773.869.1234

www.tripplite.com

Dimensions: [mm] INCHES

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.