SR2400

SmartRack® 42U Value Series Standard-Depth Rack Enclosure Cabinet



42 Rack Units 2400 lb.



Stationary

1600 lb. Rolling Load Capacity Load Capacity



Heavy-Duty Casters



Locking Doors & **Side Panels**



Standard 19 in. **Rack Width**



Toolless **Mounting Slots**



Adjustable Rails with **Easy-View** Depth Index



Airflow Exceeds Server OEM Requirements




Integrated **Baying Tabs**



Square Hole Mounting

- A Adjustable Mounting Rails
- **B** Toolless Mounting Slots
- Roof Panel (Removable)
- Front Door (Lockable/Removable/Reversible)
- **E** Split Rear Doors (Lockable/Removable)
- F Side Panels (Lockable/Removable)
- **G** Heavy-Duty Casters
- **H** Heavy-Duty Levelers
- (For doors and side panels.)

Also Includes: Owner's manual, 2 shipping/stabilizing brackets and equipment-mounting hardware (50 M6 cage nuts, 50 M6 washers, 50 M6 screws)




- **Specifications** Model SR2400 **Rack Spaces** 42U **Stationary Load Capacity** 2400 lb. (1089 kg) 1600 lb. (726 kg) **Rolling Load Capacity** Unit Dimensions (H x W x D) 78.4 x 23.6 x 41.3 in. (1991 x 599 x 1049 mm) Shipping Dimensions (H x W x D) 84.5 x 27.75 x 47 in. (2146 x 705 x 1194 mm) **Unit Weight** 265 lb. (120 kg) 288 lb. (131 kg) **Shipping Weight** Standards Meets EIA/ECA-310-E, RoHS, CE and UL 60950 (Accommodates all standard rack-mount equipment regardless of vendor.)
- Ships fully assembled for rapid deployment, but can be knocked down for easy reassembly in confined spaces
- Rolls into place on heavy-duty pre-installed removable
- Ideal for rack-mount server, network and telecom applications


SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS





1111 W. 35th Street Chicago, IL 60609 USA 773.869.1234 www.tripplite.com




Dimensions: [mm] INCHES
Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.











OPTIONAL SRCABLETRAY
AND SRCABLETRAYEXP CABLE
MANAGEMENT ACCESSORIES
SHOWN (MOUNTING
POSITION ADJUSTS TO
ACCOMMODATE A WIDE
RANGE OF APPLICATIONS)

MODEL: SR2400



1111 W. 35th Street Chicago, IL 60609 USA 773.869.1234 www.tripplite.com

Dimensions: [mm] INCHES

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

SIDE VIEW