SR42UBDP

SmartRack[™] Deep Rack Enclosure



42 Rack Units



3000 lb Stationary **Load Rating**



2250 lb Rolling **Load Rating**



Heavy-Duty Casters



Locking Doors & Side Panels



Standard 19-inch Rack Width



Toolless **Mounting Slots**



Adjustable Rails with Easy-View Depth Index



Airflow Exceeds Server OEM Requirements




Integrated **Baying Tabs**




Square Hole Mounting

- A Adjustable Mounting Rails
- **B** Adjustable PDU Mounting Rails with Toolless Mounting Slots
- C Roof Panel (Removable)
- Front Door (Lockable/Removable/Reversible)
- **E** Split Rear Doors (Lockable/Removable)
- F Side Panels (Lockable/Removable)
- **G** Heavy-Duty Casters
- **H** Heavy-Duty Levelers
- Keys (For doors and side panels.)

Also Includes: Owner's manual, 2 stabilizing brackets and rackmount equipment mounting hardware (50 cage nuts, 50 mounting screws, 50 nylon cup



Specifications



Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.








- · Ships ready for rapid deployment, but can be knocked down for easy reassembly in confined spaces
- Modular design optimized for quick configuration and reconfiguration
- · Ideal for rackmount server, network and telecom applications

SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS




1111 W. 35th Street Chicago, IL 60609 USA 773.869.1234 www.tripplite.com



Dimensions: [mm] INCHES

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.



Dimensions: [mm] INCHES

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

www.tripplite.com