MODEL: SR42UBEXPNDNR3 SmartRack[®] Heavy-Duty Open Frame Rack















EIA







42 Rack Units

3000 lb. Stationary Load Capacity

3000 lb. Rolling Load Capacity

Rolling Casters

Toolless **Rack Width** Mounting Slots

Adjustable Rails with Easy-View Depth Index

Integrated **Baying Tabs**

Square Hole Mounting

Adjustable Mounting Rails (4)

- B Adjustable PDU Mounting Rails with Toolless Mounting Slots (2) (Hold up to 4 vertical PDUs.)
- C 3-Inch Heavy-Duty Casters (4)
- D Heavy-Duty Levelers (4)

. Snecifications


Also Includes: Owner's manual, 2 shipping/stabilizing brackets and rackmount equipment mounting hardware (50 cage nuts, 50 mounting screws, 50 nylon cup washers).

- Rack ships fully assembled for rapid deployment, but can be knocked down for easy reassembly in confined spaces
- Modular design optimized for quick configuration and reconfiguration
- · Ideal for rackmount server, network and telecom applications



specifications	- ROHS
Model	SR42UBEXPNDNR3
Rack Spaces	42U
Stationary Load Capacity	3000 lb. (1361 kg)
Rolling Load Capacity	3000 lb. (1361 kg)
Unit Dimensions (H x W x D)	78.5 x 23.63 x 43.5 in. (1994 x 600 x 1092 mm)
Shipping Dimensions (H x W x D)	79 x 24.5 x 40 in. (2007 x 622 x 1016 mm)
Unit Weight	150 lb. (68 kg)
Shipping Weight	200 lb. (90.7 kg)
Certifications	EIA-310-E, IEC 60297-3-100, UL 60950,
	RoHS, NOM
Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.	

Also Available: Shock pallet models with special packaging to facilitate equipment pre-installation and reshipment to final site. Heavy-duty shock pallet holds up to 1250 lb. (568 kg), including the weight of the rack and pre-installed equipment. Add "SP1" to model numbers above to order shock pallet models.



SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS



