## SR42UW / SR42UWEXP

## SmartRack<sup>™</sup> Premium Rack Enclosure



42 Rack Units



2250 lb 3000 lb Stationary Rolling Load Capacity Load Capacity





Heavy-Duty Locking Doors & Casters Side Panels



Standard 19-inch **Rack Width** 



Toolless **Mounting Slots** 



Adjustable Rails with **Easy-View** Depth Index



Exceeds Server OEM Requirements




Integrated **Baying Tabs** 



Square Hole Mounting

- A Adjustable Mounting Rails
- **B** Adjustable PDU Mounting **Rails with Toolless Mounting Slots**
- Roof Panel (Removable)
- Front Door (Lockable/Removable/Reversible)
- **E** Split Rear Doors (Lockable/Removable)
- F Side Panels (Lockable/Removable; not included with SR42UBEXP.)
- G Heavy-Duty Casters
- **H** Heavy-Duty Levelers
- (For doors and side panels.)

Also Includes: Owner's manual, 2 shipping/stabilizing brackets and rackmount equipment mounting hardware (50 cage nuts, 50 mounting screws, 50 nylon cup washers).



Specifications	ROHS
Model	SR42UW
Rack Spaces	42U
Stationary Load Capacity	3000 lb (1363 kg)
Rolling Load Capacity	2250 lb (1022 kg)
Unit Dimensions (H x W x D)	78.5 x 23.63 x 43 in (1994 x 600 x 1092 mm)
Shipping Dimensions (H x W x D)	84.5 x 27.75 x 47 in (2146 x 705 x 1194 mm)
Unit Weight	281 lb (127.7 kg)
Shipping Weight	304 lb (138.2 kg)
Certifications	TIA/EIA-310-D Compliant (Accommodates all standard
	19-inch rackmount equipment regardless of vendor.)
Model	SR42UWEXP (Identical to SR42UW without side panels.)
Unit Weight	203 lb (92.3 kg)
Shipping Weight	226 lb (102.7 kg)
Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.	


Also Available: Shock pallet models with special packaging to facilitate equipment pre-installation and reshipment to final site. Heavy-duty shock pallet holds up to 1250 lb (568 kg), including the weight of the enclosure and pre-installed equipment. Add "SP1" to model numbers above to order shock pallet models


- Enclosures ship fully assembled for rapid deployment, but can be knocked down for easy reassembly in confined spaces
- · Modular design optimized for quick configuration and reconfiguration
- · Ideal for rackmount server, network and telecom applications


## SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS




1111 W. 35th Street Chicago, IL 60609 USA 773.869.1234 www.tripplite.com













OPTIONAL SRCABLETRAY
AND SRCABLETRAYEXP CABLE
MANAGEMENT ACCESSORIES
SHOWN (MOUNTING
POSITION ADJUSTS TO
ACCOMMODATE A WIDE
RANGE OF APPLICATIONS)

MODELS:
SR42UW
SR42UWEXE



1111 W. 35th Street Chicago, IL 60609 USA 773.869.1234 www.tripplite.com

Dimensions: [mm] INCHES

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

SIDE VIEW