MODEL:

SR4POST48HD

4-Post Heavy-Duty Open Frame Rack



48 Rack Unit



3000 lb Stationary Load Capacity



3000 lb. Rolling Load Capacity (with Optional Casters)



Standard 19-inch Rack Width



Toolless Mounting Slots




Square Hole Mounting



Side Panel Accessory (Optional)

- A Numbered Square Mounting Holes
- B Toolless Mounting Holes (for vertical PDUs or cable managers)
- PDU/Cable Management Brackets (optional, included)

Also Includes: Owner's Manual, installation hardware and (2) PDU/cable management





- Modular, self-squaring design optimized for quick configuration and reconfiguration
- Multiple units can be bolted together side by side
- Compatible with optional side panel kit (SR48SIDE4PHD) for end-row units
- Optional heavy-duty caster kit (SRCASTERHDKIT) permits mobile use with loads up to 3000 lb.

SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS

Electronic Industries Alliance
SR4POST48HD
48U
3000 lb. / 1350 kg
3000 lb. / 1350 kg*
90 x 24 x 35.25 in. / 2286 x 610 x 895 mm
6.75 x 9.5 x 93.75 in. / 172 x 241 x 2381 mm
110 lb. / 49.5 kg
117 lb. / 52.7 kg
Tested to EIA-310-D, NOM (Mexico), IEC 60297-3-100, RoHS



1111 W. 35th Street Chicago, IL 60609 USA 773.869.1234 www.tripplite.com

