## SR4POST50HD

## 4-Post Heavy-Duty Open Frame Rack



50 Rack Units



3000 lb. Stationary **Load Capacity** 



3000 lb. Rolling Load Capacity (with Optional Casters)



Standard 19-inch Rack Width



**Mounting Slots** 



Integrated **Baying Tabs** 



Mounting




Accessory (Optional)

- A Numbered Square Mounting Holes
- **Toolless Mounting Holes** (for vertical PDUs or cable managers)
- PDU/Cable Management Brackets (optional, included)

Also Includes: Owner's Manual, installation hardware and (2) PDU/cable management brackets.

reconfiguration

loads up to 3000 lb.



## SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS

Specifications	Electronic Industries Alliance
Model	SR4POST50HD
Rack Spaces	50U
Stationary Load Capacity	3000 lb. / 1361 kg
Rolling Load Capacity	3000 lb. / 1361 kg
Unit Dimensions (H x W x D)	93 x 24 x 35.25 in. / 2362 x 610 x 895 mm
Shipping Dimensions (H x W x D)	6.75 x 9.5 x 97.25 in. / 172 x 241 x 2470 mm
Unit Weight	113 lb. / 51.3 kg
Shipping Weight	120 lb. / 54.4 kg
Standards	Tested to EIA-310-D, NOM (Mexico), IEC 60297-3-100, DIN 41494, RoHS

Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.



1111 W. 35th Street Chicago, IL 60609 USA 773.869.1234 www.tripplite.com

