
MODEL: SRW10USG

SmartRack[®] Wall-Mount Rack Enclosure Cabinet



Floor-Standing Installation: Optional SRCASTER kit adapts cabinet to roll under desks, tables or counters. (Kit includes 4 casters.)

B




Specifications 6	UMPLIANT	COMPLIANT
Model	SRW10USG	
Rack Spaces	10U	
Equipment Mounting Depth	Up to 20.5 in. / 521 mm	1
Load Rating*	200 lb. / 90.7 kg	
Unit Dimensions (H x W x D)	21.58 x 23.62 x 21.5 in.	/ 548 x 600 x 546 mm
Shipping Dimensions (H x W x	D) 24.25 x 26.38 x 24.13 in	. / 616 x 670 x 613 mm
Unit Weight	53.4 lb. / 24 kg	
Shipping Weight	59.2 lb. / 27 kg	
Standards	Meets EIA-310-E, NOM, IEC 60297-3-100 and D IP20 Protection Rating	
* The load rating includes the combined mounted to a stable surface with user-		


- Wall-mount enclosures provide convenient, locking storage for rackmount IT devices and other equipment that should be off the floor, out of the way and secure
- The cabinet is fully reversible, allowing installers to change door hinges from left to right by simply rotating the unit 180 degrees before mounting
- Hinged wall bracket allows cabinet to swing away from the wall for convenient access to equipment and cabling
- Front door shatter-resistant clear acrylic window allows for easier equipment readouts without unlocking the enclosure


SEE NEXT PAGE FOR DETAILED UNIT MEASUREMENTS















REAR VIEW





Dimensions: [mm] INCHES Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

