



NOTE:

1. CABLE: UL2725 USB 2.0 CABLE 28AWG*1P+20AWG*2C+AEB(AL) OD: ø4.8mm BLACK PVC JACKET.
2. CONNECTORS:
 - P1: USB B TYPE MALE
 - P2: USB B TYPE PANEL MOUNT FEMALE



REV	DESCRIPTION OF CHANGE			DATE									
	<table border="1"> <tr> <th>TOLERANCE INCHES</th> <th>M/M</th> </tr> <tr> <td>.X</td> <td>.015 .30</td> </tr> <tr> <td>.XX</td> <td>.010 .10</td> </tr> <tr> <td>.XXX</td> <td>.005 .05</td> </tr> </table>			TOLERANCE INCHES	M/M	.X	.015 .30	.XX	.010 .10	.XXX	.005 .05		
TOLERANCE INCHES	M/M												
.X	.015 .30												
.XX	.010 .10												
.XXX	.005 .05												
	SCALE	NONE		REV									
	UNIT	MM											
DRAWN BY	SHEET	1/1	DWG NO.										
	DATE	05/20/19											
CHECK BY	TITLE USB B M TO USB B F												
APPD BY	PART NO. U025-XXX-PM												