



## OMNIVS1500XL Estimated Runtime

UPS	Battery Pack Model	Battery Pack Qty	Load in WATTS													
			20	50	100	150	200	250	300	350	400	500	600	700	800	940
OMNIVS1500XL	Included Batteries	0	308	149	74	47	34	26	20	17	14	10	8.0	6.3	5.1	4.0
OMNIVS1500XL	BP24V12RT2U	1	859	443	233	153	111	86	70	58	49	37	29	24	20	16

Supports up to 940W using internal batteries or 1 BP24V12RT2U. All runtime values are shown in minutes.

UPS	Battery Pack Model	Battery Pack Qty	Load in WATTS													
			20	50	80	100	150	200	250	300	350	400	450	500	550	600
OMNIVS1500XL	BP24V28-2U	1	1,393	738	492	399	267	197	154	125	105	90	78	68	60	54
OMNIVS1500XL	BP24V70-3U	1	2,878	1,592	1,090	896	614	462	368	303	257	222	194	171	152	136
OMNIVS1500XL	BP24V70-3U	2	5,004	2,904	2,034	1,691	1,183	904	727	606	518	451	398	353	316	285
OMNIVS1500XL	BP24V70-3U	3	6,785	4,087	2,913	2,441	1,730	1,334	1,081	906	778	681	604	538	482	437
OMNIVS1500XL	BP24V70-3U	4	8,298	5,159	3,733	3,148	2,255	1,750	1,426	1,201	1,035	908	807	721	649	589
OMNIVS1500XL	BP24V70-3U	5	9,600	6,135	4,498	3,815	2,758	2,154	1,763	1,489	1,287	1,132	1,009	903	814	740
OMNIVS1500XL	BP24V70-3U	6	10,731	7,027	5,215	4,446	3,242	2,545	2,091	1,772	1,535	1,352	1,207	1,083	977	890
OMNIVS1500XL	BP24V70-3U	7	11,724	7,846	5,887	5,044	3,707	2,925	2,411	2,048	1,778	1,569	1,403	1,260	1,139	1,038
OMNIVS1500XL	BP24V70-3U	8	12,602	8,600	6,519	5,610	4,154	3,292	2,723	2,318	2,017	1,783	1,596	1,436	1,299	1,185
OMNIVS1500XL	BP24V70-3U	9	13,384	9,297	7,114	6,148	4,584	3,649	3,027	2,583	2,251	1,993	1,787	1,609	1,457	1,330
OMNIVS1500XL	BP24V70-3U	10	14,085	9,942	7,675	6,660	4,998	3,995	3,323	2,842	2,481	2,199	1,974	1,779	1,613	1,474

Supports up to 600W using BP24V28-2U or BP24V70-3U battery packs. All runtime values are shown in minutes.