



## OMNIVS1500XLTA A Estimated Runtime

UPS	Battery Pack Model	Battery Pack Qty	Load in WATTS													
			20	50	100	150	200	250	300	350	400	500	600	700	800	940
OMNIVS1500XLTA A	Included Batteries	0	308	149	74	47	34	26	20	17	14	10	8.0	6.3	5.1	4.0
OMNIVS1500XLTA A	BP24V12RT2U	1	859	443	233	153	111	86	70	58	49	37	29	24	20	16

*Supports up to 940W using internal batteries or 1 BP24V12RT2U. All runtime values are shown in minutes.*

UPS	Battery Pack Model	Battery Pack Qty	Load in WATTS													
			20	50	80	100	150	200	250	300	350	400	450	500	550	600
OMNIVS1500XLTA A	BP24V28-2U	1	1,393	738	492	399	267	197	154	125	105	90	78	68	60	54
OMNIVS1500XLTA A	BP24V70-3U	1	2,878	1,592	1,090	896	614	462	368	303	257	222	194	171	152	136
OMNIVS1500XLTA A	BP24V70-3U	2	5,004	2,904	2,034	1,691	1,183	904	727	606	518	451	398	353	316	285
OMNIVS1500XLTA A	BP24V70-3U	3	6,785	4,087	2,913	2,441	1,730	1,334	1,081	906	778	681	604	538	482	437
OMNIVS1500XLTA A	BP24V70-3U	4	8,298	5,159	3,733	3,148	2,255	1,750	1,426	1,201	1,035	908	807	721	649	589
OMNIVS1500XLTA A	BP24V70-3U	5	9,600	6,135	4,498	3,815	2,758	2,154	1,763	1,489	1,287	1,132	1,009	903	814	740
OMNIVS1500XLTA A	BP24V70-3U	6	10,731	7,027	5,215	4,446	3,242	2,545	2,091	1,772	1,535	1,352	1,207	1,083	977	890
OMNIVS1500XLTA A	BP24V70-3U	7	11,724	7,846	5,887	5,044	3,707	2,925	2,411	2,048	1,778	1,569	1,403	1,260	1,139	1,038
OMNIVS1500XLTA A	BP24V70-3U	8	12,602	8,600	6,519	5,610	4,154	3,292	2,723	2,318	2,017	1,783	1,596	1,436	1,299	1,185
OMNIVS1500XLTA A	BP24V70-3U	9	13,384	9,297	7,114	6,148	4,584	3,649	3,027	2,583	2,251	1,993	1,787	1,609	1,457	1,330
OMNIVS1500XLTA A	BP24V70-3U	10	14,085	9,942	7,675	6,660	4,998	3,995	3,323	2,842	2,481	2,199	1,974	1,779	1,613	1,474

*Supports up to 600W using BP24V28-2U or BP24V70-3U battery packs. All runtime values are shown in minutes.*