



S3M10K-NIB Estimated Runtime

| UPS Model | Battery Pack Model | Battery Pack Qty | Load in Kilowatts (kW) | | | | | | | | | |
|------------|--------------------|------------------|------------------------|-------|-------|-----|-----|-----|-----|-----|-----|------|
| | | | 1kW | 2kW | 3kW | 4kW | 5kW | 6kW | 7kW | 8kW | 9kW | 10kW |
| S3M10K-NIB | BP240V09 | 1 | 448 | 209 | 131 | 93 | 70 | 56 | 46 | 39 | 33 | 29 |
| S3M10K-NIB | BP240V09 | 2 | 930 | 455 | 292 | 211 | 163 | 132 | 109 | 93 | 80 | 70 |
| S3M10K-NIB | BP240V09K | 1 | 448 | 209 | 131 | 93 | 70 | 56 | 46 | 39 | 33 | 29 |
| S3M10K-NIB | BP240V09K | 2 | 930 | 455 | 292 | 211 | 163 | 132 | 109 | 93 | 80 | 70 |
| S3M10K-NIB | BP240V40 | 1 | 502 | 236 | 148 | 105 | 80 | 64 | 53 | 45 | 38 | 33 |
| S3M10K-NIB | BP240V40 | 2 | 1,035 | 510 | 329 | 238 | 184 | 149 | 124 | 106 | 91 | 80 |
| S3M10K-NIB | BP240V40 | 3 | 1,551 | 782 | 512 | 376 | 293 | 239 | 200 | 171 | 149 | 131 |
| S3M10K-NIB | BP240V40L | 1 | 1,035 | 510 | 329 | 238 | 184 | 149 | 124 | 106 | 91 | 80 |
| S3M10K-NIB | BP240V40L | 2 | 2,047 | 1,050 | 695 | 514 | 404 | 330 | 278 | 239 | 208 | 184 |
| S3M10K-NIB | BP240V40L | 3 | 2,984 | 1,572 | 1,055 | 788 | 625 | 515 | 436 | 376 | 330 | 293 |
| S3M10K-NIB | BP240V65 | 1 | 837 | 407 | 260 | 188 | 144 | 116 | 97 | 82 | 71 | 62 |
| S3M10K-NIB | BP240V65 | 2 | 1,676 | 849 | 558 | 410 | 321 | 262 | 220 | 188 | 163 | 144 |
| S3M10K-NIB | BP240V65 | 3 | 2,465 | 1,281 | 854 | 634 | 501 | 411 | 347 | 299 | 261 | 231 |
| S3M10K-NIB | BP240V65L | 1 | 1,676 | 849 | 558 | 410 | 321 | 262 | 220 | 188 | 163 | 144 |
| S3M10K-NIB | BP240V65L | 2 | 3,207 | 1,700 | 1,144 | 856 | 680 | 561 | 476 | 411 | 360 | 320 |
| S3M10K-NIB | BP240V100 | 1 | 1,295 | 646 | 420 | 307 | 239 | 194 | 162 | 138 | 120 | 105 |

All runtime values are shown in minutes.