



S3M15K-NIB Estimated Runtime

UPS Model	Battery Pack Model	Battery Pack Qty	Load in Kilowatts (kW)									
			1.5kW	3kW	4.5kW	6kW	7.5kW	9kW	10.5kW	12kW	13.5kW	15kW
S3M15K-NIB	BP240V09	1	289	131	80	56	42	33	27	23	20	17
S3M15K-NIB	BP240V09	2	616	292	184	132	101	80	66	56	48	42
S3M15K-NIB	BP240V09K	1	289	131	80	56	42	33	27	23	20	17
S3M15K-NIB	BP240V09K	2	616	292	184	132	101	80	66	56	48	42
S3M15K-NIB	BP240V40	1	325	148	91	64	49	38	31	26	23	20
S3M15K-NIB	BP240V40	2	688	329	208	149	114	91	75	64	55	48
S3M15K-NIB	BP240V40	3	1,045	512	330	239	185	149	123	105	91	80
S3M15K-NIB	BP240V40L	1	688	329	208	149	114	91	75	64	55	48
S3M15K-NIB	BP240V40L	2	1,394	695	453	330	257	208	174	148	128	113
S3M15K-NIB	BP240V40L	3	2,065	1,055	697	515	405	330	277	237	207	183
S3M15K-NIB	BP240V65	1	552	260	164	116	89	71	58	49	42	37
S3M15K-NIB	BP240V65	2	1,133	558	361	262	203	163	136	115	100	88
S3M15K-NIB	BP240V65	3	1,692	854	560	411	322	261	218	187	162	143
S3M15K-NIB	BP240V65L	1	1,133	558	361	262	203	163	136	115	100	88
S3M15K-NIB	BP240V65L	2	2,228	1,144	758	561	442	360	303	260	227	201
S3M15K-NIB	BP240V100	1	868	420	269	194	149	120	99	84	72	63

All runtime values are shown in minutes.