



## S3M200KX Estimated Runtime

UPS Model	Battery Pack Model	Battery Pack Qty	Load in Kilowatts (kW)													
			10kW	20kW	30kW	40kW	50kW	60kW	70kW	80kW	90kW	100kW	120kW	140kW	160kW	180kW
S3M200KX	BP480V40	1	59	28	17	12	9.1	7.1	5.7	4.7	4.0	3.4	2.5	1.9	1.5	1.2
S3M200KX	BP480V40	2	139	68	43	30	23	18	15	13	11	9.4	7.3	5.8	4.8	4.0
S3M200KX	BP480V40	3	223	112	71	51	39	31	26	22	19	16	13	10	8.6	7.3
S3M200KX	BP480V40	4	309	157	101	73	56	45	37	32	27	24	19	15	13	11
S3M200KX	BP480V40	5	395	204	133	96	74	60	49	42	36	32	25	21	17	15
S3M200KX	BP480V40	6	482	252	165	120	93	75	62	53	46	40	32	26	22	19
S3M200KX	BP480V40	7	569	300	197	144	112	90	75	64	56	49	39	32	27	23
S3M200KX	BP480V40	8	655	348	230	168	131	106	89	76	66	58	46	38	32	27
S3M200KX	BP480V40	9	741	396	263	193	151	123	102	87	76	67	53	44	37	32
S3M200KX	BP480V40	10	827	444	296	218	171	139	116	100	87	76	61	50	42	37
S3M200KX	BP480V40	11	912	492	329	243	191	156	130	112	97	86	68	57	48	41
S3M200KX	BP480V40	12	997	541	363	269	211	172	145	124	108	95	76	63	53	46
S3M200KX	BP480V200	1	88	42	26	19	14	11	9.0	7.5	6.4	5.5	4.2	3.3	2.6	2.2
S3M200KX	BP480V200	2	202	100	64	46	35	28	23	19	17	14	11	9.2	7.6	6.4
S3M200KX	BP480V200	3	320	163	105	76	58	47	39	33	28	25	20	16	13	11
S3M200KX	BP480V200	4	439	228	148	108	83	67	56	47	41	36	28	23	20	17
S3M200KX	BP480V200	5	558	294	193	141	109	88	74	63	54	48	38	31	26	22
S3M200KX	BP480V200	6	677	360	238	175	136	110	92	79	68	60	48	39	33	29
S3M200KX	BP480V200	7	795	426	283	209	163	133	111	95	83	73	58	48	40	35
S3M200KX	BP480V200	8	912	492	329	243	191	156	130	112	97	86	68	57	48	41
S3M200KX	BP480V200	9	1,029	559	375	278	219	179	150	129	112	99	79	66	56	48
S3M200KX	BP480V200	10	1,144	625	421	313	247	202	170	146	127	112	90	75	63	55
S3M200KX	BP480V200	11	1,259	691	467	348	275	225	190	163	143	126	101	84	71	62
S3M200KX	BP480V200	12	1,373	756	513	383	303	249	210	181	158	140	113	93	79	69
S3M200KX	BP480V65	1	108	52	33	23	18	14	11	10	8.1	7.0	5.4	4.3	3.5	2.9
S3M200KX	BP480V65	2	244	123	79	56	43	34	28	24	21	18	14	12	10	8.2
S3M200KX	BP480V65	3	385	198	129	93	72	58	48	41	35	31	24	20	17	14
S3M200KX	BP480V65	4	526	276	181	132	102	82	69	58	51	44	35	29	24	21
S3M200KX	BP480V65	5	666	354	234	171	134	108	90	77	67	59	47	39	33	28
S3M200KX	BP480V65	6	806	432	288	212	166	135	113	96	84	74	59	49	41	35
S3M200KX	BP480V65	7	944	510	342	253	198	162	136	116	101	89	71	59	50	43
S3M200KX	BP480V65	8	1,081	589	396	294	231	189	159	136	119	105	84	70	59	51
S3M200KX	BP480V65	9	1,217	667	450	335	265	217	183	157	137	121	97	81	68	59
S3M200KX	BP480V65	10	1,352	745	505	377	298	245	206	178	155	137	110	92	78	67
S3M200KX	BP480V65	11	1,485	822	559	418	332	273	230	198	174	154	124	103	88	76
S3M200KX	BP480V65	12	1,617	899	613	460	365	301	254	219	192	170	137	114	97	84
S3M200KX	BP480V300	1	135	66	41	29	22	18	15	12	10	9.0	7.0	5.6	4.6	3.8
S3M200KX	BP480V300	2	300	153	98	71	54	44	36	31	26	23	18	15	12	11
S3M200KX	BP480V300	3	469	244	160	116	90	72	60	51	44	39	31	25	21	18
S3M200KX	BP480V300	4	638	338	223	163	127	103	86	73	64	56	44	37	31	27
S3M200KX	BP480V300	5	806	432	288	212	166	135	113	96	84	74	59	49	41	35
S3M200KX	BP480V300	6	972	526	353	261	205	167	140	120	105	92	74	61	52	45
S3M200KX	BP480V300	7	1,136	620	418	311	245	200	168	145	126	111	89	74	63	54
S3M200KX	BP480V300	8	1,298	713	483	360	285	234	197	169	148	131	105	87	74	64
S3M200KX	BP480V300	9	1,459	807	548	410	325	267	226	194	170	150	121	101	86	74
S3M200KX	BP480V300	10	1,617	899	613	460	365	301	254	219	192	170	137	114	97	84
S3M200KX	BP480V300	11	1,774	991	678	510	405	335	283	245	215	190	154	128	109	95
S3M200KX	BP480V300	12	1,929	1,082	742	560	446	368	312	270	237	210	171	142	121	105
S3M200KX	BP480V100	1	180	89	57	40	31	25	20	17	15	13	10	8.0	6.6	5.6
S3M200KX	BP480V100	2	395	204	133	96	74	60	49	42	36	32	25	21	17	15
S3M200KX	BP480V100	3	612	324	213	156	121	98	82	70	61	53	42	35	29	25
S3M200KX	BP480V100	4	827	444	296	218	171	139	116	100	87	76	61	50	42	37
S3M200KX	BP480V100	5	1,039	565	379	281	221	181	152	130	114	100	80	66	56	49
S3M200KX	BP480V100	6	1,249	685	463	345	272	223	188	162	141	125	100	83	71	61
S3M200KX	BP480V100	7	1,455	804	546	409	324	266	225	194	169	150	121	100	85	74
S3M200KX	BP480V100	8	1,658	923	630	473	375	309	262	226	198	175	142	118	100	87
S3M200KX	BP480V100	9	1,857	1,040	713	537	427	353	299	258	227	201	163	136	116	101
S3M200KX	BP480V100	10	2,054	1,157	795	600	479	396	336	291	256	227	184	154	132	114
S3M200KX	BP480V100	11	2,248	1,273	878	664	531	440	374	324	285	253	206	172	147	128
S3M200KX	BP480V100	12	2,439	1,388	959	727	582	483	411	357	314	279	227	191	163	142

All runtime values are shown in minutes.