



S3M30KXD-NIB Estimated Runtime

UPS Model	Battery Pack Model	Battery Pack Qty	Load in Kilowatts (kW)													
			2.5kW	5kW	7.5kW	10kW	12kW	14kW	16kW	18kW	20kW	22kW	24kW	25kW	26kW	27kW
S3M30KXD-NIB	BP480V40	1	367	172	108	76	61	50	43	37	32	28	25	24	23	22
S3M30KXD-NIB	BP480V40	2	771	379	243	175	142	118	101	87	77	68	61	58	56	53
S3M30KXD-NIB	BP480V40	3	1,167	588	383	280	228	191	164	143	126	112	101	96	92	88
S3M30KXD-NIB	BP480V40	4	1,552	795	524	385	316	266	229	200	177	158	143	136	130	124
S3M30KXD-NIB	BP480V200	1	519	249	157	112	90	75	64	55	48	43	38	36	35	33
S3M30KXD-NIB	BP480V200	2	1,069	535	348	253	206	173	148	129	113	101	91	87	83	79
S3M30KXD-NIB	BP480V200	3	1,599	820	541	398	327	275	237	207	183	164	148	141	135	129
S3M30KXD-NIB	BP480V200	4	2,109	1,101	733	544	448	379	328	287	255	229	208	198	189	181
S3M30KXD-NIB	BP480V65	1	620	301	191	137	111	92	78	68	59	53	47	45	43	41
S3M30KXD-NIB	BP480V65	2	1,264	640	418	306	250	210	180	157	138	124	111	106	101	97
S3M30KXD-NIB	BP480V65	3	1,880	974	646	478	393	332	286	251	223	200	180	172	164	157
S3M30KXD-NIB	BP480V65	4	2,468	1,301	872	650	537	455	394	347	308	277	251	240	230	220
S3M30KXD-NIB	BP480V300	1	751	369	236	170	138	115	98	85	74	66	59	56	54	51
S3M30KXD-NIB	BP480V300	2	1,514	774	510	375	307	258	222	194	172	154	139	132	126	121
S3M30KXD-NIB	BP480V300	3	2,236	1,171	782	581	479	406	351	308	274	246	223	213	203	195
S3M30KXD-NIB	BP480V300	4	2,918	1,557	1,050	786	651	554	481	423	378	340	309	295	282	271
S3M30KXD-NIB	BP480V100	1	970	483	313	227	185	154	132	115	101	90	81	77	73	70
S3M30KXD-NIB	BP480V100	2	1,926	999	664	491	404	341	295	258	229	205	186	177	169	162
S3M30KXD-NIB	BP480V100	3	2,816	1,499	1,009	755	625	531	461	406	362	326	296	282	270	259
S3M30KXD-NIB	BP480V100	4	3,645	1,980	1,347	1,014	844	720	627	554	495	447	407	389	373	357

All runtime values are shown in minutes.