



## S3M40KXD Estimated Runtime

UPS Model	Battery Pack Model	Battery Pack Qty	Load in Kilowatts (kW)													
			2.5kW	5kW	7.5kW	10kW	12kW	14kW	16kW	18kW	21kW	24kW	27kW	30kW	33kW	36kW
S3M40KXD	Internal Batteries	0	163	73	44	31	24	20	16	14	11	9.3	7.8	6.7	5.7	5.0
S3M40KXD	BP480V10	1	361	171	107	76	61	50	42	37	30	25	22	19	17	15
S3M40KXD	BP480V10	2	561	272	173	124	100	83	71	61	50	43	37	32	28	25
S3M40KXD	BP480V10	3	760	376	242	175	141	118	100	87	72	61	53	46	41	37
S3M40KXD	BP480V10	4	956	479	311	226	184	154	131	114	95	81	70	61	54	49
S3M40KXD	BP480V10	5	1,150	583	381	278	227	190	163	142	118	101	87	77	68	61
S3M40KXD	BP480V10	6	1,341	686	451	331	270	227	195	170	142	122	106	93	83	74
S3M40KXD	BP480V10	7	1,530	788	520	383	314	265	228	199	167	143	124	109	97	88
S3M40KXD	BP480V10	8	1,716	890	590	436	358	302	261	228	191	164	143	126	112	101
S3M40KXD	BP480V10	9	1,899	991	660	489	402	340	294	257	216	185	162	143	128	115
S3M40KXD	BP480V10	10	2,080	1,092	729	541	446	378	327	287	241	207	181	160	143	129

All runtime values are shown in minutes.