



S3M50K-60KWR4T Estimated Runtime

UPS Model	Battery Pack Model	Battery Pack Qty	Load in Kilowatts (kW)									
			5kW	10kW	15kW	20kW	25kW	30kW	35kW	40kW	45kW	50kW
S3M50K-60KWR4T	BP240V40L	1	182	80	48	33	25	20	16	14	12	10
S3M50K-60KWR4T	BP240V40L	2	399	183	113	80	60	48	40	34	29	25
S3M50K-60KWR4T	BP240V40L	3	618	291	183	130	100	80	66	56	49	43
S3M50K-60KWR4T	BP240V65	1	143	62	37	25	19	15	12	10	8.7	7.5
S3M50K-60KWR4T	BP240V65	2	317	143	88	62	47	37	30	26	22	19
S3M50K-60KWR4T	BP240V65	3	495	230	143	102	77	62	51	43	37	33
S3M50K-60KWR4T	BP240V65L	1	318	144	88	62	47	37	30	26	22	19
S3M50K-60KWR4T	BP240V65L	2	674	319	201	144	110	88	73	62	54	47
S3M50K-60KWR4T	BP240V65L	3	1,024	498	319	231	178	144	120	102	89	78
S3M50K-60KWR4T	BP240V100	1	236	105	64	44	33	26	22	18	16	14
S3M50K-60KWR4T	BP240V100	2	509	237	148	105	80	64	53	45	39	34
S3M50K-60KWR4T	BP240V100	3	781	373	237	170	131	105	87	74	64	56
S3M50K-60KWR4T	BP240V100L	1	509	237	148	105	80	64	53	45	39	34
S3M50K-60KWR4T	BP240V100L	2	1,049	510	328	237	183	148	124	106	92	81

All runtime values are shown in minutes.