



SM2200RMDVTAA Estimated Runtime

Load in Watts

UPS	Battery Pack	BP Qty.	200W	400W	600W	800W	1000W	1100W	1200W	1300W	1400W	1500W	1600W	1700W	1800W	1920W
SM2200RMDVTAA	Included Batteries	0	173	81	51	36	28	24	21	19	17	15	14	13.1	12.6	12.0
SM2200RMDVTAA	BP48V24-2U	1	484	242	156	112	86	76	68	61	55	50	46	43	40	36
SM2200RMDVTAA	BP48V60RT3U	1	611	310	201	146	112	99	89	80	73	66	61	56	52	48
SM2200RMDVTAA	BP48V60RT3U	2	1090	570	378	278	217	193	173	157	143	131	121	112	105	96
SM2200RMDVTAA	BP48V60RT3U	3	1554	829	556	414	325	290	261	237	217	200	185	172	160	148
SM2200RMDVTAA	BP48V60RT3U	4	2003	1084	734	549	434	388	351	319	293	270	250	233	217	201
SM2200RMDVTAA	BP48V60RT3U	5	2436	1334	910	684	542	487	440	402	369	341	316	295	276	255
SM2200RMDVTAA	BP48V60RT3U	6	2854	1580	1084	818	651	585	530	484	445	412	382	357	334	310
SM2200RMDVTAA	BP48V60RT3U	7	3258	1822	1255	952	759	683	620	567	522	483	449	419	393	365
SM2200RMDVTAA	BP48V60RT3U	8	3650	2059	1425	1083	866	780	709	649	598	554	515	482	452	420
SM2200RMDVTAA	BP48V60RT3U	9	4028	2291	1593	1214	973	877	798	731	674	625	582	544	510	475
SM2200RMDVTAA	BP48V60RT3U	10	4394	2520	1758	1344	1079	974	886	812	750	695	648	606	569	530

All runtime values are in minutes.