



## SMART1000RMX2UN Estimated Runtime

UPS	Battery Configuration	CONNECTED EQUIPMENT LOAD IN WATTS													
		20	40	60	100	150	200	250	300	400	500	600	700	800	900
SMART1000RMX2UN	INCLUDED BATTERIES	266	190	145	95	65	48	37	30	21	15	12	9.3	7.6	6.3

UPS	External Battery Pack	BP QTY	CONNECTED EQUIPMENT LOAD IN WATTS													
			20	40	60	100	150	200	250	300	400	500	600	700	750	800
SMART1000RMX2UN	1 BP36V15-2U	1	874	645	508	351	248	189	152	125	92	70	56	46	42	39
SMART1000RMX2UN	1 BP36V27-2US	1	1,171	871	689	480	343	264	212	176	130	100	80	66	60	55
SMART1000RMX2UN	2 BP36V27-2US	1	2,025	1,528	1,222	866	629	489	398	334	250	195	157	130	120	111
SMART1000RMX2UN	3 BP36V27-2US	2	2,825	2,154	1,736	1,244	911	715	585	493	372	293	237	198	183	169
SMART1000RMX2UN	4 BP36V27-2US	3	3,575	2,750	2,230	1,611	1,189	938	771	652	495	392	319	267	247	229
SMART1000RMX2UN	5 BP36V27-2US	4	4,281	3,319	2,705	1,968	1,461	1,157	955	810	618	491	401	338	312	290
SMART1000RMX2UN	6 BP36V27-2US	5	4,945	3,861	3,163	2,316	1,728	1,374	1,137	967	741	590	484	408	378	352
SMART1000RMX2UN	7 BP36V27-2US	6	5,571	4,379	3,604	2,654	1,990	1,587	1,316	1,122	862	689	566	479	444	413
SMART1000RMX2UN	8 BP36V27-2US	7	6,162	4,875	4,028	2,983	2,246	1,796	1,493	1,275	983	787	648	549	509	475
SMART1000RMX2UN	9 BP36V27-2US	8	6,722	5,349	4,438	3,304	2,497	2,002	1,668	1,427	1,102	885	730	619	575	536
SMART1000RMX2UN	10 BP36V27-2US	9	7,252	5,803	4,833	3,616	2,743	2,205	1,840	1,576	1,221	982	812	689	641	598
SMART1000RMX2UN	1 BP36V42-3U	10	2,134	1,613	1,292	917	667	520	423	355	266	208	167	139	128	118
SMART1000RMX2UN	2 BP36V42-3U	1	3,768	2,904	2,359	1,707	1,262	997	820	695	528	418	341	286	264	245
SMART1000RMX2UN	3 BP36V42-3U	2	5,200	4,071	3,341	2,453	1,834	1,459	1,209	1,029	789	630	517	436	404	376
SMART1000RMX2UN	4 BP36V42-3U	3	6,465	5,130	4,249	3,155	2,381	1,906	1,586	1,356	1,047	840	692	587	544	508
SMART1000RMX2UN	5 BP36V42-3U	4	7,591	6,096	5,089	3,819	2,905	2,339	1,954	1,675	1,300	1,047	866	736	684	639
SMART1000RMX2UN	6 BP36V42-3U	5	8,599	6,979	5,869	4,447	3,407	2,756	2,311	1,987	1,548	1,251	1,038	884	823	769
SMART1000RMX2UN	7 BP36V42-3U	6	9,508	7,791	6,596	5,042	3,888	3,160	2,658	2,291	1,792	1,452	1,208	1,031	960	898
SMART1000RMX2UN	8 BP36V42-3U	7	10,330	8,539	7,274	5,606	4,351	3,550	2,996	2,589	2,031	1,651	1,375	1,177	1,097	1,026
SMART1000RMX2UN	9 BP36V42-3U	8	11,078	9,230	7,908	6,141	4,795	3,928	3,324	2,879	2,266	1,846	1,541	1,321	1,232	1,154
SMART1000RMX2UN	10 BP36V42-3U	9	11,762	9,872	8,502	6,651	5,222	4,294	3,644	3,162	2,496	2,038	1,705	1,463	1,366	1,280

All runtime values are shown in minutes.