



SMART1500CRMXL Estimated Runtime

UPS	Battery Pack	BP Qty.	Load in Watts													
			100	200	300	400	500	600	700	800	900	1,000	1,100	1,200	1,300	1,440
SMART1500CRMXL	Included Batteries	0	166	78	47	32	24	18	15	12	11	9.3	8.3	7.5	6.8	6.0
SMART1500CRMXL	BP48V24-2U	1	579	298	194	141	109	88	73	61	53	46	40	36	32	28
SMART1500CRMXL	BP48V27-2US	1	784	410	270	197	154	125	104	88	75	66	58	52	47	41
SMART1500CRMXL	BP48V27-2US	2	1,382	744	500	372	293	240	202	172	148	130	115	103	93	82
SMART1500CRMXL	BP48V27-2US	3	1,954	1,074	730	547	435	358	303	259	225	198	176	158	144	127
SMART1500CRMXL	BP48V27-2US	4	2,503	1,396	957	722	576	477	405	348	303	267	239	215	195	173
SMART1500CRMXL	BP48V27-2US	5	3,028	1,710	1,181	895	717	596	508	437	381	337	302	273	248	220
SMART1500CRMXL	BP48V27-2US	6	3,531	2,017	1,401	1,067	857	714	610	526	460	408	365	331	301	267
SMART1500CRMXL	BP48V27-2US	7	4,013	2,317	1,617	1,236	996	832	712	615	539	478	429	389	355	315
SMART1500CRMXL	BP48V27-2US	8	4,476	2,609	1,831	1,403	1,134	949	813	703	617	549	493	447	408	363
SMART1500CRMXL	BP48V27-2US	9	4,920	2,895	2,040	1,569	1,270	1,064	914	792	695	619	557	505	462	412
SMART1500CRMXL	BP48V27-2US	10	5,348	3,175	2,247	1,732	1,405	1,179	1,014	879	773	689	620	563	515	460
SMART1500CRMXL	BP48V60RT-3U*	1	1,145	611	408	301	237	193	162	137	118	104	92	82	74	65
SMART1500CRMXL	BP48V60RT-3U*	2	2,066	1,139	775	582	463	382	324	277	240	212	189	170	154	136
SMART1500CRMXL	BP48V60RT-3U*	3	2,925	1,648	1,136	861	689	572	487	419	365	323	289	261	237	210
SMART1500CRMXL	BP48V60RT-3U*	4	3,726	2,138	1,488	1,135	913	761	651	561	491	436	391	354	323	287
SMART1500CRMXL	BP48V60RT-3U*	5	4,476	2,609	1,831	1,403	1,134	949	813	703	617	549	493	447	408	363
SMART1500CRMXL	BP48V60RT-3U*	6	5,179	3,064	2,164	1,667	1,351	1,133	974	844	742	661	595	540	494	441
SMART1500CRMXL	BP48V60RT-3U*	7	5,839	3,501	2,490	1,925	1,565	1,316	1,133	984	866	773	696	633	580	518
SMART1500CRMXL	BP48V60RT-3U*	8	6,460	3,923	2,807	2,178	1,776	1,496	1,290	1,122	989	884	797	726	665	595
SMART1500CRMXL	BP48V60RT-3U*	9	7,046	4,330	3,115	2,427	1,983	1,674	1,446	1,259	1,112	994	898	818	750	672
SMART1500CRMXL	BP48V60RT-3U*	10	7,599	4,723	3,416	2,670	2,187	1,849	1,600	1,395	1,233	1,103	997	909	835	748

All runtime values are shown in minutes. * BP48V48RT-4U can be substituted for BP48V60RT3U with the same runtime performance.