



## SMART2600RM2U Estimated Runtime

UPS	Battery Pack	BP Qty.	Load in Watts													
			200	400	600	800	1,000	1,100	1,200	1,300	1,400	1,500	1,600	1,700	1,800	1,920
SMART2600RM2U	Internal batteries	0	78	36	22	16	12	11	9.3	8.3	7.4	6.7	6.1	5.5	5.1	4.6
SMART2600RM2U	BP48V24-2U	1	277	133	83	59	45	39	35	31	28	26	24	22	20	18
SMART2600RM2U	BP48V27-2US	1	382	186	118	84	64	57	50	45	41	37	34	32	29	27
SMART2600RM2U	BP48V27-2US	2	697	352	228	165	127	113	101	91	83	76	70	64	60	55
SMART2600RM2U	BP48V27-2US	3	1,007	520	341	250	194	172	155	140	128	117	108	100	93	86
SMART2600RM2U	BP48V27-2US	4	1,311	686	455	336	262	234	210	191	174	160	148	137	128	118
SMART2600RM2U	BP48V27-2US	5	1,608	852	569	422	331	296	266	242	221	204	189	175	163	151
SMART2600RM2U	BP48V27-2US	6	1,899	1,015	683	508	400	358	323	294	269	248	230	214	200	185
SMART2600RM2U	BP48V27-2US	7	2,183	1,177	795	595	469	420	380	346	318	293	272	253	236	219
SMART2600RM2U	BP48V27-2US	8	2,461	1,338	907	681	539	483	437	399	366	338	314	292	273	253
SMART2600RM2U	BP48V27-2US	9	2,733	1,496	1,019	766	608	546	494	451	415	383	356	332	311	288
SMART2600RM2U	BP48V27-2US	10	2,999	1,652	1,129	851	677	608	551	504	463	428	398	371	348	323
SMART2600RM2U	BP48V60RT-3U	1	571	285	184	132	102	90	80	72	66	60	55	51	47	43
SMART2600RM2U	BP48V60RT-3U	2	1,068	553	364	267	207	184	166	150	137	125	116	107	100	92
SMART2600RM2U	BP48V60RT-3U	3	1,549	819	546	405	317	283	255	232	212	195	180	167	156	144
SMART2600RM2U	BP48V60RT-3U	4	2,013	1,080	728	543	428	383	346	315	289	266	247	229	214	198
SMART2600RM2U	BP48V60RT-3U	5	2,461	1,338	907	681	539	483	437	399	366	338	314	292	273	253
SMART2600RM2U	BP48V60RT-3U	6	2,893	1,590	1,085	817	649	583	529	483	444	410	381	356	333	309
SMART2600RM2U	BP48V60RT-3U	7	3,310	1,838	1,260	953	759	683	620	567	522	483	449	419	393	365
SMART2600RM2U	BP48V60RT-3U	8	3,713	2,080	1,434	1,087	868	782	710	650	599	555	516	482	452	421
SMART2600RM2U	BP48V60RT-3U	9	4,103	2,319	1,605	1,220	977	880	801	734	676	627	584	546	512	477
SMART2600RM2U	BP48V60RT-3U	10	4,479	2,553	1,773	1,352	1,084	978	891	817	753	699	651	609	572	533

All runtime values are shown in minutes.