



SMART3000CRMXL Estimated Runtime

UPS	Battery Configuration	Load in Watts													
		100	200	400	600	800	1,100	1,400	1,700	2,000	2,300	2,600	2,880	3,300	3,600
SMART3000CRMXL	Internal batteries	310	160	77	49	36	25	20	15	12	10	8.6	7.5	6.1	5.1

Maximum load 2880 watts with L5-30P input plug. Maximum load 3600 watts with hardwire input.

UPS	Battery Pack	BP Qty.	Load in Watts													
			100	200	400	600	800	1,100	1,300	1,500	1,700	2,100	2,300	2,500	2,700	2,880
SMART3000CRMXL	BP48V24-2U	1	646	340	164	103	73	50	40	34	29	22	20	18	16	15
SMART3000CRMXL	BP48V27-2US	1	815	435	213	135	97	66	54	45	38	29	26	24	21	20
SMART3000CRMXL	BP48V27-2US	2	1,313	718	361	234	169	117	96	81	70	53	48	43	39	36
SMART3000CRMXL	BP48V27-2US	3	1,794	997	511	335	245	171	141	119	103	79	71	64	59	54
SMART3000CRMXL	BP48V27-2US	4	2,257	1,271	661	437	322	226	187	159	137	107	96	87	79	73
SMART3000CRMXL	BP48V27-2US	5	2,704	1,540	809	539	399	282	234	199	173	135	122	110	100	93
SMART3000CRMXL	BP48V27-2US	6	3,135	1,803	956	640	476	339	282	240	209	163	148	134	122	113
SMART3000CRMXL	BP48V27-2US	7	3,551	2,061	1,102	741	553	395	330	282	245	192	174	158	144	134
SMART3000CRMXL	BP48V27-2US	8	3,952	2,314	1,246	842	630	452	377	323	282	221	201	182	167	155
SMART3000CRMXL	BP48V27-2US	9	4,341	2,562	1,389	942	706	508	425	365	318	251	228	207	190	176
SMART3000CRMXL	BP48V27-2US	10	4,716	2,805	1,531	1,041	783	565	474	406	355	280	255	232	212	197
SMART3000CRMXL	BP48V48RT4U*	1	1,116	605	302	194	140	96	79	66	57	43	39	35	32	29
SMART3000CRMXL	BP48V48RT4U*	2	1,888	1,052	541	355	260	182	150	127	110	85	76	69	63	58
SMART3000CRMXL	BP48V48RT4U*	3	2,616	1,487	780	518	383	271	225	191	166	129	116	105	96	89
SMART3000CRMXL	BP48V48RT4U*	4	3,303	1,907	1,015	681	507	361	301	257	223	175	158	143	131	121
SMART3000CRMXL	BP48V48RT4U*	5	3,952	2,314	1,246	842	630	452	377	323	282	221	201	182	167	155
SMART3000CRMXL	BP48V48RT4U*	6	4,567	2,708	1,474	1,001	752	542	454	390	340	268	244	222	203	189
SMART3000CRMXL	BP48V48RT4U*	7	5,150	3,090	1,698	1,159	874	632	531	456	399	316	287	262	240	223
SMART3000CRMXL	BP48V48RT4U*	8	5,703	3,461	1,918	1,315	995	722	608	523	459	364	331	302	277	258
SMART3000CRMXL	BP48V48RT4U*	9	6,229	3,819	2,135	1,470	1,114	811	684	590	518	411	375	342	314	293
SMART3000CRMXL	BP48V48RT4U*	10	6,729	4,167	2,347	1,622	1,233	900	760	656	577	459	419	383	352	328

Maximum load 2880 watts with external battery packs. All runtime values are shown in minutes.

*BP48V60RT3U can be substituted for BP48V48RT-4U with the same runtime performance