



## SMART3000CRMXLN Estimated Runtime

UPS	Battery Configuration	CONNECTED EQUIPMENT LOAD IN WATTS													
		100	200	400	600	800	1,100	1,440	1,700	2,000	2,300	2,600	2,880	3,300	3,600
SMART3000CRMXLN	Internal Batteries	310	160	77	49	36	25	19	15	12	10	8.6	7.5	6.1	5.1

Maximum load 2880 watts with NEMA L5-30P input plug. Maximum load 3600 watts with hardwire input.

UPS	External Battery Pack	BP QTY	CONNECTED EQUIPMENT LOAD IN WATTS													
			100	200	400	600	800	1,100	1,300	1,440	1,700	2,100	2,300	2,500	2,700	2,880
SMART3000CRMXLN	BP48V24-2U	1	646	340	164	103	73	50	40	36	29	22	20	18	16	15
SMART3000CRMXLN	BP48V27-2US	1	815	435	213	135	97	66	54	47	38	29	26	24	21	20
SMART3000CRMXLN	BP48V27-2US	2	1,313	718	361	234	169	117	96	85	70	54	48	43	39	36
SMART3000CRMXLN	BP48V27-2US	3	1,794	997	511	335	245	171	141	125	103	80	71	64	59	54
SMART3000CRMXLN	BP48V27-2US	4	2,257	1,271	661	437	322	226	187	166	137	107	96	87	79	73
SMART3000CRMXLN	BP48V27-2US	5	2,704	1,540	809	539	399	282	234	209	173	135	122	110	100	93
SMART3000CRMXLN	BP48V27-2US	6	3,135	1,803	956	640	476	339	282	251	209	164	148	134	122	113
SMART3000CRMXLN	BP48V27-2US	7	3,551	2,061	1,102	741	553	395	330	295	245	193	174	158	144	134
SMART3000CRMXLN	BP48V27-2US	8	3,952	2,314	1,246	842	630	452	377	338	282	222	201	182	167	155
SMART3000CRMXLN	BP48V27-2US	9	4,341	2,562	1,389	942	706	508	425	381	318	252	228	207	190	176
SMART3000CRMXLN	BP48V27-2US	10	4,716	2,805	1,531	1,041	783	565	474	425	355	282	255	232	212	197
SMART3000CRMXLN	BP48V48RT-4U	1	1,116	605	302	194	140	96	79	70	57	44	39	35	32	29
SMART3000CRMXLN	BP48V48RT-4U	2	1,888	1,052	541	355	260	182	150	133	110	85	76	69	63	58
SMART3000CRMXLN	BP48V48RT-4U	3	2,616	1,487	780	518	383	271	225	200	166	130	116	105	96	89
SMART3000CRMXLN	BP48V48RT-4U	4	3,303	1,907	1,015	681	507	361	301	269	223	176	158	143	131	121
SMART3000CRMXLN	BP48V48RT-4U	5	3,952	2,314	1,246	842	630	452	377	338	282	222	201	182	167	155
SMART3000CRMXLN	BP48V48RT-4U	6	4,567	2,708	1,474	1,001	752	542	454	407	340	270	244	222	203	189
SMART3000CRMXLN	BP48V48RT-4U	7	5,150	3,090	1,698	1,159	874	632	531	477	399	318	287	262	240	223
SMART3000CRMXLN	BP48V48RT-4U	8	5,703	3,461	1,918	1,315	995	722	608	546	459	365	331	302	277	258
SMART3000CRMXLN	BP48V48RT-4U	9	6,229	3,819	2,135	1,470	1,114	811	684	615	518	413	375	342	314	293
SMART3000CRMXLN	BP48V48RT-4U	10	6,729	4,167	2,347	1,622	1,233	900	760	684	577	461	419	383	352	328

\*BP48V60RT3U can be substituted for BP48V48RT-4U with equal runtime performance. All runtime values are shown in minutes.