



## SMART3000NET Estimated Runtime

UPS	Battery Pack	BP Qty.	Load in Watts													
			200	400	500	600	700	800	1,000	1,200	1,400	1,600	1,800	2,000	2,200	2,400
SMART3000NET	Internal batteries	0	169	79	62	50	42	36	28	23	18	14	12	10	8.3	7.0
SMART3000NET	BP24V28-2U	1	335	158	122	99	82	70	53	42	34	29	24	21	19	16
SMART3000NET	BP24V70-3U	1	597	291	228	186	156	133	102	82	67	56	48	42	37	33

Maximum load 2400 watts without external battery packs or with 1 external battery pack. All runtime values are shown in minutes.

UPS	Battery Pack	BP Qty.	Load in Watts													
			200	300	400	500	600	700	800	900	1,000	1,100	1,200	1,300	1,400	1,600
SMART3000NET	BP24V70-3U	2	1,026	692	517	409	336	284	245	215	190	170	154	139	127	107
SMART3000NET	BP24V70-3U	3	1,443	985	741	591	489	415	359	316	281	253	229	208	190	161

Maximum load 1600 watts with 2 or 3 external battery packs. All runtime values are shown in minutes.

UPS	Battery Pack	BP Qty.	Load in Watts													
			200	250	300	350	400	500	600	700	800	900	1,000	1,100	1,200	1,250
SMART3000NET	BP24V70-3U	4	1,848	1,508	1,272	1,097	963	771	641	546	474	418	373	336	306	291
SMART3000NET	BP24V70-3U	5	2,240	1,836	1,553	1,343	1,182	950	792	677	589	521	466	420	383	365
SMART3000NET	BP24V70-3U	6	2,620	2,156	1,828	1,585	1,398	1,127	941	806	704	623	558	505	460	439
SMART3000NET	BP24V70-3U	7	2,989	2,468	2,098	1,823	1,610	1,302	1,090	935	817	725	650	589	537	513
SMART3000NET	BP24V70-3U	8	3,347	2,772	2,362	2,056	1,818	1,474	1,237	1,063	930	826	742	672	614	586
SMART3000NET	BP24V70-3U	9	3,695	3,068	2,621	2,285	2,024	1,644	1,382	1,189	1,042	927	833	756	691	660
SMART3000NET	BP24V70-3U	10	4,032	3,358	2,874	2,510	2,226	1,812	1,525	1,315	1,154	1,026	924	838	767	733

Maximum load 1250 watts with 4 or more external battery packs. All runtime values are shown in minutes.