



SMART3000RMLN Estimated Runtime

| UPS | Extended Battery Module | EBM QTY | CONNECTED EQUIPMENT LOAD IN WATTS | | | | | | | | | | | | | | | | | | | | |
|---------------|----------------------------|------------|-----------------------------------|-------|-------|-----|-----|-----|-----|-----|-----|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| | | | 150 | 200 | 300 | 400 | 500 | 600 | 700 | 800 | 900 | 1,000 | 1,200 | 1,300 | 1,500 | 2,000 | 2,200 | 2,300 | 2,500 | 2,600 | 2,700 | 2,800 | 3,000 |
| SMART3000RMLN | Internal batteries | n/a | 162 | 116 | 74 | 53 | 41 | 33 | 28 | 24 | 21 | 18 | 14 | 12 | 10 | 6 | 5 | 5 | 4 | 4 | 4 | 4 | 3 |
| SMART3000RMLN | BP72VRM2U | 1 | 603 | 434 | 273 | 197 | 152 | 123 | 103 | 88 | 77 | 68 | 54 | 49 | 41 | 29 | 26 | 24 | 22 | 21 | 20 | 19 | 17 |
| SMART3000RMLN | BP72VRM2U | 2 | 1,112 | 799 | 503 | 363 | 281 | 228 | 190 | 163 | 142 | 125 | 100 | 91 | 77 | 54 | 48 | 45 | 41 | 39 | 37 | 35 | 33 |
| SMART3000RMLN | BP72VRM2U | 3 | 1,663 | 1,196 | 753 | 543 | 420 | 341 | 285 | 244 | 212 | 187 | 150 | 137 | 115 | 81 | 72 | 68 | 61 | 58 | 56 | 53 | 49 |
| SMART3000RMLN | BP72VRM2U | 4 | 2,247 | 1,615 | 1,017 | 733 | 568 | 460 | 385 | 329 | 287 | 253 | 203 | 185 | 155 | 109 | 97 | 92 | 83 | 79 | 75 | 72 | 67 |

All runtime values are shown in minutes.