



SMART3000VS Estimated Runtime

UPS	Battery Pack	Load in Watts													
		20	50	100	200	400	600	800	1,000	1,200	1,400	1,600	1,800	2,000	2,250
SMART3000VS	INCLUDED BATTERIES	479	279	158	81	40	26	19	16	13	9.7	7.7	6.2	5.1	4.0
SMART3000VS	1 BP48V27-2US	1953	1195	712	381	186	118	84	64	51	42	35	30	26	22
SMART3000VS	2 BP48V27-2US	3279	2064	1262	694	351	227	165	127	102	84	71	61	53	46
SMART3000VS	3 BP48V27-2US	4472	2877	1790	1003	517	340	249	194	157	129	110	95	83	71
SMART3000VS	4 BP48V27-2US	5551	3639	2298	1306	684	453	334	262	213	177	150	130	114	99
SMART3000VS	5 BP48V27-2US	6530	4354	2786	1603	848	567	420	331	270	225	192	166	146	127
SMART3000VS	6 BP48V27-2US	7424	5027	3255	1892	1012	680	506	400	327	273	234	203	179	155
SMART3000VS	7 BP48V27-2US	8243	5661	3706	2176	1173	792	592	469	385	322	276	240	212	185
SMART3000VS	8 BP48V27-2US	8996	6259	4140	2453	1333	904	678	539	442	371	318	278	246	214
SMART3000VS	9 BP48V27-2US	9690	6824	4559	2724	1490	1015	763	608	500	420	361	316	280	244
SMART3000VS	10 BP48V27-2US	10333	7359	4962	2989	1646	1125	848	677	558	469	404	353	313	274
SMART3000VS	1 BP48V60RT-3U	2765	1723	1044	569	284	183	132	101	81	67	56	48	42	36
SMART3000VS	2 BP48V60RT-3U	4696	3033	1893	1064	551	363	266	207	168	139	118	102	89	77
SMART3000VS	3 BP48V60RT-3U	6342	4214	2690	1544	816	544	403	317	258	215	183	159	140	121
SMART3000VS	4 BP48V60RT-3U	7760	5285	3437	2006	1076	725	541	428	350	293	250	218	192	167
SMART3000VS	5 BP48V60RT-3U	8996	6259	4140	2453	1333	904	678	539	442	371	318	278	246	214
SMART3000VS	6 BP48V60RT-3U	10082	7149	4803	2884	1584	1081	814	649	535	450	387	338	300	262
SMART3000VS	7 BP48V60RT-3U	11044	7965	5427	3300	1831	1256	949	759	627	528	455	399	354	310
SMART3000VS	8 BP48V60RT-3U	11901	8717	6018	3702	2073	1428	1083	868	718	607	524	460	409	358
SMART3000VS	9 BP48V60RT-3U	12671	9411	6577	4090	2311	1599	1216	977	810	685	592	520	463	406
SMART3000VS	10 BP48V60RT-3U	13366	10055	7107	4466	2544	1767	1347	1084	900	763	660	581	518	454

All runtime values are shown in minutes.