



SMART750RMXL2UN Estimated Runtime

UPS	Battery Configuration	CONNECTED EQUIPMENT LOAD IN WATTS													
		20	40	60	100	150	200	250	300	350	400	450	500	550	600
SMART750RMXL2UN	INCLUDED BATTERIES	226	147	106	67	44	33	25	21	17	14	12	11	10	8.5

UPS	External Battery Pack	BP QTY	CONNECTED EQUIPMENT LOAD IN WATTS													
			10	20	30	40	50	80	100	150	200	250	300	350	400	450
SMART750RMXL2UN	BP24V15RT2U	1	840	642	516	430	366	250	205	137	101	79	64	53	45	39
SMART750RMXL2UN	BP24V28-2U	1	1,364	1,054	855	717	615	427	352	240	180	142	116	96	82	71
SMART750RMXL2UN	BP24V36-2US	1	1,619	1,256	1,022	859	739	516	426	293	220	174	143	119	101	88
SMART750RMXL2UN	BP24V36-2US	2	2,822	2,222	1,828	1,550	1,344	954	796	558	425	340	282	237	203	177
SMART750RMXL2UN	BP24V36-2US	3	3,917	3,119	2,587	2,208	1,923	1,381	1,159	821	630	508	424	358	309	270
SMART750RMXL2UN	BP24V36-2US	4	4,917	3,953	3,302	2,832	2,478	1,795	1,513	1,080	834	676	566	480	415	365
SMART750RMXL2UN	BP24V36-2US	5	5,834	4,731	3,976	3,426	3,008	2,196	1,857	1,334	1,035	843	708	602	522	460
SMART750RMXL2UN	BP24V36-2US	6	6,677	5,458	4,613	3,992	3,516	2,584	2,193	1,584	1,234	1,007	848	723	628	555
SMART750RMXL2UN	BP24V36-2US	7	7,455	6,139	5,215	4,530	4,003	2,961	2,519	1,829	1,430	1,170	988	843	734	649
SMART750RMXL2UN	BP24V36-2US	8	8,176	6,778	5,786	5,045	4,470	3,326	2,838	2,069	1,623	1,331	1,126	963	840	743
SMART750RMXL2UN	BP24V36-2US	9	8,845	7,379	6,327	5,536	4,919	3,680	3,148	2,305	1,813	1,490	1,263	1,082	944	837
SMART750RMXL2UN	BP24V36-2US	10	9,469	7,946	6,842	6,005	5,350	4,024	3,450	2,537	2,001	1,648	1,398	1,199	1,048	930
SMART750RMXL2UN	BP24V70-3U	1	2,822	2,222	1,828	1,550	1,344	954	796	558	425	340	282	237	203	177
SMART750RMXL2UN	BP24V70-3U	2	4,917	3,953	3,302	2,832	2,478	1,795	1,513	1,080	834	676	566	480	415	365
SMART750RMXL2UN	BP24V70-3U	3	6,677	5,458	4,613	3,992	3,516	2,584	2,193	1,584	1,234	1,007	848	723	628	555
SMART750RMXL2UN	BP24V70-3U	4	8,176	6,778	5,786	5,045	4,470	3,326	2,838	2,069	1,623	1,331	1,126	963	840	743
SMART750RMXL2UN	BP24V70-3U	5	9,469	7,946	6,842	6,005	5,350	4,024	3,450	2,537	2,001	1,648	1,398	1,199	1,048	930
SMART750RMXL2UN	BP24V70-3U	6	10,594	8,985	7,797	6,885	6,163	4,682	4,032	2,988	2,367	1,957	1,665	1,432	1,254	1,114
SMART750RMXL2UN	BP24V70-3U	7	11,584	9,916	8,666	7,694	6,917	5,303	4,586	3,422	2,724	2,258	1,926	1,660	1,457	1,297
SMART750RMXL2UN	BP24V70-3U	8	12,460	10,755	9,459	8,440	7,618	5,891	5,114	3,841	3,070	2,553	2,183	1,885	1,657	1,477
SMART750RMXL2UN	BP24V70-3U	9	13,241	11,516	10,186	9,130	8,272	6,447	5,618	4,245	3,406	2,841	2,434	2,105	1,853	1,654
SMART750RMXL2UN	BP24V70-3U	10	13,942	12,208	10,855	9,771	8,883	6,975	6,098	4,635	3,733	3,122	2,680	2,322	2,047	1,829

All runtime values are shown in minutes.