



SMARTINT3000VS Estimated Runtime

UPS	Battery Pack	BP Qty.	Load in Watts													
			200	400	500	600	700	800	900	1,000	1,200	1,400	1,600	1,800	2,000	2,250
SMARTINT3000VS	Internal batteries	0	81	40	32	26	22	19	17	16	13	10	7.7	6.2	5.1	4.0
SMARTINT3000VS	BP48V27-2US	1	381	186	145	118	98	84	73	64	51	42	35	30	26	22
SMARTINT3000VS	BP48V60RT-3U	1	569	284	224	183	154	132	115	101	81	67	56	48	42	36

Maximum load 2250 watts without external battery packs or with 1 external battery pack. All runtime values are shown in minutes.

UPS	Battery Pack	BP Qty.	Load in Watts													
			200	300	400	500	600	700	800	900	1,000	1,100	1,200	1,300	1,400	1,500
SMARTINT3000VS	BP48V27-2US	2	694	470	351	277	227	192	165	144	127	114	102	92	84	77
SMARTINT3000VS	BP48V27-2US	3	1,003	687	517	412	340	288	249	218	194	174	157	142	129	119
SMARTINT3000VS	BP48V27-2US	4	1,306	902	684	547	453	386	334	294	262	236	213	193	177	162
SMARTINT3000VS	BP48V27-2US	5	1,603	1,114	848	681	567	484	420	371	331	298	270	245	225	207
SMARTINT3000VS	BP48V27-2US	6	1,892	1,323	1,012	815	680	581	506	448	400	361	327	298	273	252
SMARTINT3000VS	BP48V27-2US	7	2,176	1,529	1,173	948	792	679	592	524	469	424	385	351	322	297
SMARTINT3000VS	BP48V27-2US	8	2,453	1,732	1,333	1,079	904	776	678	601	539	487	442	404	371	343
SMARTINT3000VS	BP48V27-2US	9	2,724	1,932	1,490	1,209	1,015	872	763	677	608	550	500	457	420	389
SMARTINT3000VS	BP48V27-2US	10	2,989	2,128	1,646	1,338	1,125	968	848	753	677	613	558	510	469	434
SMARTINT3000VS	BP48V60RT-3U	2	1,064	731	551	439	363	307	266	233	207	186	168	152	139	127
SMARTINT3000VS	BP48V60RT-3U	3	1,544	1,072	816	654	544	464	403	355	317	286	258	235	215	198
SMARTINT3000VS	BP48V60RT-3U	4	2,006	1,406	1,076	868	725	620	541	478	428	386	350	319	293	270
SMARTINT3000VS	BP48V60RT-3U	5	2,453	1,732	1,333	1,079	904	776	678	601	539	487	442	404	371	343
SMARTINT3000VS	BP48V60RT-3U	6	2,884	2,050	1,584	1,287	1,081	930	814	723	649	588	535	489	450	416
SMARTINT3000VS	BP48V60RT-3U	7	3,300	2,360	1,831	1,492	1,256	1,082	949	844	759	689	627	574	528	489
SMARTINT3000VS	BP48V60RT-3U	8	3,702	2,663	2,073	1,693	1,428	1,233	1,083	964	868	789	718	658	607	563
SMARTINT3000VS	BP48V60RT-3U	9	4,090	2,958	2,311	1,892	1,599	1,382	1,216	1,084	977	888	810	742	685	636
SMARTINT3000VS	BP48V60RT-3U	10	4,466	3,246	2,544	2,087	1,767	1,530	1,347	1,202	1,084	987	900	826	763	708

Maximum load 1500 watts with 2 or more external battery packs. All runtime values are shown in minutes.