



SMX1200XLHG Estimated Runtime

UPS	Battery Pack	BP Qty.	Load in Watts													
			50	100	150	200	300	350	400	450	500	550	600	650	700	750
SMX1200XLHG	Internal batteries	1	249	128	82	59	36	30	25	22	19	17	15	13	12	11
SMX1200XLHG	BP36V15-2U	1	821	448	301	223	143	120	102	88	77	68	61	55	50	45
SMX1200XLHG	BP36V27-2US	1	1,101	610	414	309	200	168	144	124	109	97	87	78	71	65
SMX1200XLHG	BP36V27-2US	2	1,910	1,089	752	569	376	319	275	239	211	188	170	154	141	129
SMX1200XLHG	BP36V27-2US	3	2,670	1,552	1,084	827	554	473	408	357	316	283	256	233	214	197
SMX1200XLHG	BP36V27-2US	4	3,386	2,000	1,409	1,081	731	626	542	476	423	379	344	314	288	266
SMX1200XLHG	BP36V27-2US	5	4,061	2,433	1,726	1,331	906	778	676	594	529	476	432	395	363	336
SMX1200XLHG	BP36V27-2US	6	4,699	2,850	2,035	1,577	1,079	929	809	712	635	572	520	476	438	406
SMX1200XLHG	BP36V27-2US	7	5,302	3,254	2,338	1,818	1,250	1,078	940	829	741	668	608	557	514	476
SMX1200XLHG	BP36V27-2US	8	5,873	3,645	2,633	2,054	1,419	1,226	1,071	946	846	764	696	638	589	546
SMX1200XLHG	BP36V27-2US	9	6,415	4,023	2,921	2,287	1,586	1,372	1,200	1,061	950	859	783	719	664	616
SMX1200XLHG	BP36V27-2US	10	6,930	4,389	3,202	2,515	1,751	1,517	1,328	1,176	1,053	953	870	799	739	686
SMX1200XLHG	BP36V42-3U	1	2,014	1,152	797	604	400	340	292	255	225	201	181	164	150	138
SMX1200XLHG	BP36V42-3U	2	3,570	2,117	1,494	1,149	777	666	578	507	451	405	367	335	308	285
SMX1200XLHG	BP36V42-3U	3	4,944	3,014	2,157	1,674	1,147	989	861	759	677	611	555	509	469	434
SMX1200XLHG	BP36V42-3U	4	6,166	3,848	2,787	2,179	1,508	1,304	1,140	1,007	901	815	742	681	629	584
SMX1200XLHG	BP36V42-3U	5	7,259	4,627	3,386	2,664	1,859	1,612	1,413	1,252	1,122	1,016	928	853	788	732
SMX1200XLHG	BP36V42-3U	6	8,242	5,354	3,956	3,131	2,201	1,914	1,681	1,492	1,340	1,215	1,111	1,022	946	880
SMX1200XLHG	BP36V42-3U	7	9,132	6,036	4,499	3,580	2,534	2,208	1,943	1,727	1,554	1,411	1,291	1,190	1,102	1,026
SMX1200XLHG	BP36V42-3U	8	9,941	6,676	5,017	4,013	2,858	2,496	2,200	1,959	1,764	1,604	1,470	1,355	1,257	1,171
SMX1200XLHG	BP36V42-3U	9	10,679	7,278	5,512	4,430	3,174	2,777	2,452	2,187	1,972	1,794	1,646	1,519	1,410	1,315
SMX1200XLHG	BP36V42-3U	10	11,356	7,845	5,985	4,832	3,481	3,051	2,699	2,410	2,176	1,982	1,819	1,680	1,561	1,456

All runtime values are shown in minutes.