



## SMX3000XLRT2UA Estimated Runtime

UPS	Battery Configuration		Load in Watts													
			200	400	600	800	1,000	1,200	1,400	1,600	1,800	2,000	2,200	2,400	2,600	2,700
SMX3000XLRT2UA	Internal batteries		85	41	27	19	15	13	11	9	7	6	5	5	4	4
SMX3000XLRT2UA	BP48V24-2U	1	275	135	85	61	46	37	30	25	21	18	16	14	13	12
SMX3000XLRT2UA	BP48V27-2US	1	375	187	120	86	66	53	43	36	31	27	23	21	19	18
SMX3000XLRT2UA	BP48V27-2US	2	676	349	228	166	129	104	86	72	62	54	47	42	38	36
SMX3000XLRT2UA	BP48V27-2US	3	972	512	339	249	195	159	132	111	95	83	73	65	59	56
SMX3000XLRT2UA	BP48V27-2US	4	1,264	675	451	334	263	215	180	151	130	114	101	90	81	77
SMX3000XLRT2UA	BP48V27-2US	5	1,549	837	563	419	331	272	228	193	166	146	129	116	105	100
SMX3000XLRT2UA	BP48V27-2US	6	1,828	997	675	505	400	329	277	235	203	178	158	142	129	123
SMX3000XLRT2UA	BP48V27-2US	7	2,101	1,155	786	590	469	387	326	277	240	211	188	169	153	146
SMX3000XLRT2UA	BP48V27-2US	8	2,369	1,311	896	675	537	444	375	320	277	244	218	196	178	170
SMX3000XLRT2UA	BP48V27-2US	9	2,631	1,466	1,005	759	606	502	425	362	315	278	248	223	202	193
SMX3000XLRT2UA	BP48V27-2US	10	2,887	1,619	1,114	843	675	560	474	405	353	311	278	250	228	217
SMX3000XLRT2UA	BP48V60RT-3U	1	556	284	184	133	103	83	69	57	49	42	37	33	30	28
SMX3000XLRT2UA	BP48V60RT-3U	2	1,031	545	362	266	208	170	141	119	102	89	79	70	63	60
SMX3000XLRT2UA	BP48V60RT-3U	3	1,492	804	541	402	317	260	218	185	159	139	124	111	100	95
SMX3000XLRT2UA	BP48V60RT-3U	4	1,938	1,060	719	539	427	352	296	252	218	191	170	153	138	132
SMX3000XLRT2UA	BP48V60RT-3U	5	2,369	1,311	896	675	537	444	375	320	277	244	218	196	178	170
SMX3000XLRT2UA	BP48V60RT-3U	6	2,785	1,558	1,071	810	647	537	454	388	338	298	266	239	217	208
SMX3000XLRT2UA	BP48V60RT-3U	7	3,188	1,800	1,244	944	756	629	534	457	398	352	314	284	258	247
SMX3000XLRT2UA	BP48V60RT-3U	8	3,577	2,038	1,414	1,076	865	720	612	525	458	405	363	328	298	286
SMX3000XLRT2UA	BP48V60RT-3U	9	3,954	2,272	1,583	1,208	973	812	691	593	518	459	412	372	339	325
SMX3000XLRT2UA	BP48V60RT-3U	10	4,319	2,501	1,749	1,338	1,080	902	769	661	579	513	460	417	380	364

All runtime values are shown in minutes.