



SU10000RT3UTAA Estimated Runtime

UPS	Battery Pack	Battery Pack Qty	Load in Watts													
			1,000	1,500	2,000	2,500	3,000	3,500	4,000	4,500	5,000	5,500	6,000	7,000	8,000	9,000
SU10000RT3UTAA	Included Batteries	0	77	48	34	26	21	17	15	12	11	9.4	8.2	6.5	5.3	4.3
SU10000RT3UTAA	BP240V10RT3UTAA	1	175	111	79	61	49	40	34	29	26	23	20	16	14	12
SU10000RT3UTAA	BP240V10RT3UTAA	2	278	180	130	100	81	67	57	49	43	38	34	28	23	20
SU10000RT3UTAA	BP240V10RT3UTAA	3	383	250	182	142	114	95	81	70	62	55	49	40	34	29
SU10000RT3UTAA	BP240V10RT3UTAA	4	489	322	236	184	149	125	107	93	81	72	65	54	45	39
SU10000RT3UTAA	BP240V10RT3UTAA	5	594	394	290	227	185	155	133	116	102	91	81	67	57	49
SU10000RT3UTAA	BP240V10RT3UTAA	6	699	466	345	271	221	186	160	139	123	109	98	81	69	60
SU10000RT3UTAA	BP240V10RT3UTAA	7	803	538	400	315	258	217	187	163	144	128	116	96	81	70
SU10000RT3UTAA	BP240V10RT3UTAA	8	907	610	454	359	295	248	214	187	165	148	133	111	94	81
SU10000RT3UTAA	BP240V10RT3UTAA	9	1010	682	509	403	331	280	241	211	187	167	151	126	107	93
SU10000RT3UTAA	BP240V10RT3UTAA	10	1112	753	564	447	368	312	269	236	209	187	169	141	120	104
SU10000RT3UTAA	BP240V787C-1PH	1	873	586	436	344	282	238	205	179	158	141	127	106	90	78
SU10000RT3UTAA	BP240V787C-1PH	2	1743	1198	907	726	602	513	445	393	349	314	285	239	205	179
SU10000RT3UTAA	BP240V787C-1PH	3	2559	1786	1365	1100	919	787	687	608	543	490	446	377	325	285
SU10000RT3UTAA	BP240V787C-1PH	4	3325	2347	1808	1466	1229	1057	925	821	736	666	608	516	446	393
SU10000RT3UTAA	BP240V787C-1PH	5	4044	2885	2236	1821	1533	1322	1160	1032	927	841	768	654	568	500

All runtime values are shown in minutes.