



SU1000RTXL2UA Estimated Runtime

UPS	Battery Pack	BP qty	Load in Watts													
			20	50	100	200	300	400	450	500	550	600	650	700	750	800
SU1000RTXL2UA	Internal batteries	0	180	126	62	31	20	14	12	10	9.2	8.0	7.3	6.4	5.9	4.5
SU1000RTXL2UA	BP24V15RT2U	1	631	410	188	92	58	41	36	31	28	24	22	20	19	17
SU1000RTXL2UA	BP24V28-2U	1	1,071	708	337	169	108	78	69	59	54	47	43	39	36	33
SU1000RTXL2UA	BP24V36-2US	1	1,358	911	442	226	146	106	94	80	73	64	59	53	49	45
SU1000RTXL2UA	BP24V36-2US	2	2,392	1,639	825	436	288	212	189	163	149	131	122	109	102	93
SU1000RTXL2UA	BP24V36-2US	3	3,347	2,329	1,199	646	433	321	289	250	229	203	188	169	159	145
SU1000RTXL2UA	BP24V36-2US	4	4,230	2,982	1,564	854	578	432	389	338	310	275	256	231	217	198
SU1000RTXL2UA	BP24V36-2US	5	5,050	3,602	1,918	1,060	722	542	489	426	392	349	325	294	276	252
SU1000RTXL2UA	BP24V36-2US	6	5,813	4,191	2,263	1,263	865	652	590	515	474	422	394	357	335	307
SU1000RTXL2UA	BP24V36-2US	7	6,524	4,751	2,599	1,463	1,007	762	690	603	555	496	463	420	395	362
SU1000RTXL2UA	BP24V36-2US	8	7,189	5,284	2,926	1,660	1,148	871	789	691	637	570	532	483	455	418
SU1000RTXL2UA	BP24V36-2US	9	7,811	5,792	3,245	1,854	1,287	979	888	778	718	643	601	546	515	473
SU1000RTXL2UA	BP24V36-2US	10	8,396	6,276	3,555	2,045	1,425	1,087	987	866	799	716	670	609	574	528
SU1000RTXL2UA	BP24V70-3U	1	2,311	1,573	786	413	272	200	180	155	141	124	115	103	97	88
SU1000RTXL2UA	BP24V70-3U	2	4,136	2,899	1,509	821	554	413	374	325	298	264	246	222	208	190
SU1000RTXL2UA	BP24V70-3U	3	5,710	4,094	2,195	1,220	834	628	570	497	458	408	380	344	324	297
SU1000RTXL2UA	BP24V70-3U	4	7,080	5,176	2,846	1,608	1,109	841	765	670	617	552	515	468	440	404
SU1000RTXL2UA	BP24V70-3U	5	8,284	6,160	3,464	1,984	1,380	1,051	958	841	776	695	650	591	557	513
SU1000RTXL2UA	BP24V70-3U	6	9,351	7,058	4,051	2,350	1,645	1,259	1,149	1,010	934	838	784	714	673	620
SU1000RTXL2UA	BP24V70-3U	7	10,301	7,883	4,609	2,706	1,904	1,463	1,337	1,177	1,089	979	916	836	789	728
SU1000RTXL2UA	BP24V70-3U	8	11,155	8,641	5,141	3,051	2,159	1,664	1,523	1,342	1,243	1,119	1,048	957	904	834
SU1000RTXL2UA	BP24V70-3U	9	11,924	9,341	5,648	3,387	2,408	1,862	1,706	1,506	1,396	1,257	1,179	1,077	1,018	940
SU1000RTXL2UA	BP24V70-3U	10	12,623	9,990	6,132	3,714	2,653	2,057	1,886	1,667	1,547	1,394	1,308	1,196	1,131	1,046

All runtime values are shown in minutes.