



SU1000RTXL2UN Estimated Runtime

UPS	Battery Pack	Battery Pack Qty	Load in Watts													
			20	40	60	80	100	120	160	200	300	400	500	600	700	800
SU1000RTXL2UN	Internal Batteries	0	180	126	96	76	62	53	40	31	20	14	10	8.0	6.4	4.5
SU1000RTXL2UN	BP24V15RT2U	1	631	410	299	232	188	157	117	92	58	41	31	24	20	17
SU1000RTXL2UN	BP24V28-2U	1	1071	708	523	412	337	284	213	169	108	78	59	47	39	33
SU1000RTXL2UN	BP24V70-3U	1	2311	1573	1186	947	786	669	513	413	272	200	155	124	103	88
SU1000RTXL2UN	BP24V70-3U	2	4136	2899	2225	1800	1509	1297	1008	821	554	413	325	264	222	190
SU1000RTXL2UN	BP24V70-3U	3	5710	4094	3184	2601	2195	1897	1487	1220	834	628	497	408	344	297
SU1000RTXL2UN	BP24V70-3U	4	7080	5176	4072	3353	2846	2471	1951	1608	1109	841	670	552	468	404
SU1000RTXL2UN	BP24V70-3U	5	8284	6160	4896	4059	3464	3019	2397	1984	1380	1051	841	695	591	513
SU1000RTXL2UN	BP24V70-3U	6	9351	7058	5663	4725	4051	3543	2829	2350	1645	1259	1010	838	714	620
SU1000RTXL2UN	BP24V70-3U	7	10301	7883	6379	5353	4609	4045	3245	2706	1904	1463	1177	979	836	728
SU1000RTXL2UN	BP24V70-3U	8	11155	8641	7047	5947	5141	4525	3647	3051	2159	1664	1342	1119	957	834
SU1000RTXL2UN	BP24V70-3U	9	11924	9341	7674	6508	5648	4986	4036	3387	2408	1862	1506	1257	1077	940
SU1000RTXL2UN	BP24V70-3U	10	12623	9990	8262	7041	6132	5429	4413	3714	2653	2057	1667	1394	1196	1046
SU1000RTXL2UN	BP24V36-2US	1	1358	911	679	537	442	374	283	226	146	106	80	64	53	45
SU1000RTXL2UN	BP24V36-2US	2	2392	1639	1239	992	825	703	540	436	288	212	163	131	109	93
SU1000RTXL2UN	BP24V36-2US	3	3347	2329	1779	1434	1199	1028	796	646	433	321	250	203	169	145
SU1000RTXL2UN	BP24V36-2US	4	4230	2982	2296	1862	1564	1345	1047	854	578	432	338	275	231	198
SU1000RTXL2UN	BP24V36-2US	5	5050	3602	2793	2277	1918	1655	1295	1060	722	542	426	349	294	252
SU1000RTXL2UN	BP24V36-2US	6	5813	4191	3271	2677	2263	1958	1538	1263	865	652	515	422	357	307
SU1000RTXL2UN	BP24V36-2US	7	6524	4751	3730	3066	2599	2254	1777	1463	1007	762	603	496	420	362
SU1000RTXL2UN	BP24V36-2US	8	7189	5284	4171	3442	2926	2543	2011	1660	1148	871	691	570	483	418
SU1000RTXL2UN	BP24V36-2US	9	7811	5792	4596	3806	3245	2826	2241	1854	1287	979	778	643	546	473
SU1000RTXL2UN	BP24V36-2US	10	8396	6276	5006	4159	3555	3102	2467	2045	1425	1087	866	716	609	528

All runtime values are shown in minutes.