



SU1000RTLCD2U Estimated Runtime

UPS	Battery Pack	BP qty	Load in Watts													
			20	40	60	80	100	150	200	300	400	500	600	700	800	900
SU1000RTLCD2U	Internal batteries	0	244	154	111	85	69	46	34	22	16	12	9.2	7.3	5.9	4.8
SU1000RTLCD2U	BP24V15RT2U	1	687	447	327	254	207	137	101	64	45	34	27	22	19	16
SU1000RTLCD2U	BP24V28-2U	1	1,124	745	551	434	355	241	179	115	82	63	50	41	35	30
SU1000RTLCD2U	BP24V36-2US	1	1,338	892	663	524	430	293	219	141	102	78	62	51	43	37
SU1000RTLCD2U	BP24V36-2US	2	2,359	1,607	1,212	968	803	558	423	279	205	159	128	106	90	78
SU1000RTLCD2U	BP24V36-2US	3	3,303	2,285	1,740	1,401	1,169	821	627	420	311	243	197	165	141	122
SU1000RTLCD2U	BP24V36-2US	4	4,177	2,928	2,248	1,820	1,525	1,080	830	561	418	329	268	225	193	168
SU1000RTLCD2U	BP24V36-2US	5	4,988	3,539	2,736	2,225	1,872	1,334	1,031	701	526	415	340	286	246	215
SU1000RTLCD2U	BP24V36-2US	6	5,744	4,120	3,205	2,618	2,210	1,584	1,228	840	633	502	412	347	299	262
SU1000RTLCD2U	BP24V36-2US	7	6,450	4,672	3,656	2,999	2,539	1,829	1,424	978	739	588	484	409	353	310
SU1000RTLCD2U	BP24V36-2US	8	7,110	5,198	4,091	3,368	2,860	2,070	1,616	1,115	845	674	556	471	407	358
SU1000RTLCD2U	BP24V36-2US	9	7,728	5,700	4,510	3,726	3,172	2,306	1,805	1,251	951	760	627	533	461	406
SU1000RTLCD2U	BP24V36-2US	10	8,310	6,180	4,913	4,074	3,476	2,537	1,992	1,385	1,055	845	699	594	515	454
SU1000RTLCD2U	BP24V70-3U	1	2,359	1,607	1,212	968	803	558	423	279	205	159	128	106	90	78
SU1000RTLCD2U	BP24V70-3U	2	4,177	2,928	2,248	1,820	1,525	1,080	830	561	418	329	268	225	193	168
SU1000RTLCD2U	BP24V70-3U	3	5,744	4,120	3,205	2,618	2,210	1,584	1,228	840	633	502	412	347	299	262
SU1000RTLCD2U	BP24V70-3U	4	7,110	5,198	4,091	3,368	2,860	2,070	1,616	1,115	845	674	556	471	407	358
SU1000RTLCD2U	BP24V70-3U	5	8,310	6,180	4,913	4,074	3,476	2,537	1,992	1,385	1,055	845	699	594	515	454
SU1000RTLCD2U	BP24V70-3U	6	9,373	7,076	5,678	4,738	4,062	2,988	2,357	1,650	1,262	1,014	841	717	623	550
SU1000RTLCD2U	BP24V70-3U	7	10,321	7,898	6,392	5,365	4,619	3,422	2,712	1,909	1,466	1,181	982	839	730	645
SU1000RTLCD2U	BP24V70-3U	8	11,172	8,655	7,059	5,957	5,150	3,841	3,057	2,163	1,667	1,346	1,122	960	837	741
SU1000RTLCD2U	BP24V70-3U	9	11,939	9,354	7,685	6,518	5,656	4,245	3,392	2,412	1,865	1,510	1,261	1,080	943	835
SU1000RTLCD2U	BP24V70-3U	10	12,636	10,001	8,272	7,049	6,139	4,636	3,719	2,656	2,060	1,671	1,398	1,199	1,048	930

All runtime values are shown in minutes.